

JNK1 Polyclonal Antibody

Product Details

Size	100 µL
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide
Form	Liquid
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_1957800

Applications

Western Blot (WB)

Tested Dilution

1:1,000-1:2,000


Publications

6 Publications

Product Specific Information

A suggested positive control for this product is HeLa cells.

Product Images For JNK1 Polyclonal Antibody



JNK1 Antibody (LF-PA0047)

IP-MS enrichment of MAPK8 (LFQ intensity): MAPK8 was enriched 2030-fold from HEK293 lysate compared to background proteins, using the optimized IP-MS workflow with Pierce MS-Compatible Magnetic IP Kit protein A/G (Product # 90409) and MAPK8 antibody (Product # LF-PA0047). The STRING database (www.string-db.org) was used to identify the protein interactor list. See more information on IP-MS verification of antibody selectivity. {IP-MS}

View more figures on thermofisher.com

Western Blot (6)

<p>Molecules (Basel, Switzerland)</p> <p>Santamarine Shows Anti-Photoaging Properties via Inhibition of MAPK /AP-1 and Stimulation of TGF-/Smad Signaling in UVA-Irradiated HDFs.</p> <p>"Published figure using JNK1 polyclonal antibody (Product # LF-PA0047) in Western Blot"</p> <p>Authors: Oh JH,Kim J,Karadeniz F,Kim HR,Park SY,Seo Y,Kong CS</p>	<p>Year 2021</p>
<p>Experimental and therapeutic medicine</p> <p>Camellioside A, isolated from flowers, attenuates UVA-induced production of MMP-1 in HaCaT keratinocytes via suppression of MAPK activation.</p> <p>"LF-PA0047 was used in Western Blotting to indicate that CMDA may have potential antiphotphotoaging properties due to suppression of UVA-mediated MMP-1 production."</p> <p>Authors: Karadeniz F,Oh JH,Kim HR,Ko J,Kong CS</p>	<p>Year 2021</p> <p>Species Human</p>

View more WB references on thermofisher.com

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.