

VEGF Monoclonal Antibody (16F1)

Product Details

Size	200 µg
Species Reactivity	Human
Published Species	Rat
Host/Isotype	Mouse / IgG, kappa
Class	Monoclonal
Type	Antibody
Clone	16F1
Conjugate	Unconjugated
Immunogen	Full-length human recombinant protein expressed in E-coli
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	PBS
Contains	no preservative
Storage conditions	-20°C
RRID	AB_2536660

Applications	Tested Dilution	Publications
Western Blot (WB)	1-2 µg/mL	-
Immunohistochemistry (IHC)	-	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunocytochemistry (ICC/IF)	1:20-1:100	-
ELISA (ELISA)	1 µg/mL	-

Product Specific Information

The VEGF-A monoclonal antibody clone # 16F1 (Product # M808) has successfully been paired as the coating antibody in a sandwich ELISA with detection antibody P802B (biotinylated conjugate of Product # P802).

Typical dilutions for sandwich ELISA include 1 µg/mL for coating and 0.125-0.5 µg/mL for detection.

Product Images For VEGF Monoclonal Antibody (16F1)

VEGF Antibody (M808) in ICC/IF




Immunofluorescent analysis of Vascular Endothelial Growth Factor (VEGF, green) in Hela cells. The cells were fixed with 4% paraformaldehyde, permeabilized with 0.1% Triton X-100 in PBS, and blocked with 3% Blocker BSA (Product # 37525) for 30 minutes at room temperature. Cells were stained with (left panel) or without (right panel) a VEGF polyclonal antibody (Product # M808) at a dilution of 1:40 for at least 1 hour at room temperature, and then incubated with a Dylight 488 goat anti-mouse IgG secondary antibody at a dilution of 1:1000 for 45 minutes at room temperature. F-actin (both panels, red) was stained by Dylight 554 Phalloidin (Product # 21834) and nuclei (both panels, blue) were stained with DAPI (Product # 46190). Images were taken at 60X magnification.

VEGF Antibody (M808) in WB

Western blot analysis of Vascular Endothelial Growth Factor (VEGF) was performed by loading 1 µg of indicated recombinant VEGF isoforms, and 10 µL of PageRuler PlusPrestained Protein Ladder (Product # 26619) per well onto a 4-20% Tris-Glycine polyacrylamide gel. Proteins were transferred to a PVDF membrane (Product # 88518) using the G2 Fast Blotter (Product # 62288) and blocked with 5% Milk/TBST for at least 1 hour at room temperature. VEGF was detected at 14 kD, 19 kD and 22-30 kD using a VEGF monoclonal antibody (Product # M808) at a dilution of 1:1000 in blocking buffer overnight at 4C on a rocking platform, followed by an HRP-conjugated goat anti-mouse IgG (Fc) secondary antibody (Product # 31437) at a dilution of 1:20,000 for at least 1 hour. Chemiluminescent detection was performed using SuperSignal West Dura (Product # 34076).

VEGF Antibody (M808) in WB

Western blot was performed using Anti-VEGF Monoclonal Antibody (16F1) (Product # M808) and 20 and 40 kDa bands corresponding to VEGF were observed. Recombinant VEGF protein (250 ng) was electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were then transferred onto a Nitrocellulose membrane (Product # IB23002) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (1 µg/ml) and detected by chemiluminescence with Goat anti-Mouse IgG (H+L) Superclonal™ Recombinant Secondary Antibody, HRP (Product # A28177, 1:4000) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using Novex® ECL Reagent Kit (Product # WP20005).



View more figures on thermofisher.com

Immunohistochemistry (1)

Frontiers in oncology	Year 2020
Upregulation of OTUD7B (Cezanne) Promotes Tumor Progression via AKT/VEGF Pathway in Lung Squamous Carcinoma and Adenocarcinoma.	
"Published figure using VEGF monoclonal antibody (Product # M808) in Immunohistochemistry"	
Authors: Lin DD,Shen Y,Qiao S,Liu WW,Zheng L,Wang YN,Cui N,Wang YF,Zhao S,Shi JH	

Immunohistochemistry (Paraffin) (1)

Respiratory research	Year 2021
Qi-Long-Tian formula extract alleviates symptoms of acute high-altitude diseases via suppressing the inflammation responses in rat.	Species Rat
"M808 was used in Immunohistochemistry (Paraffin) to clarify the therapeutic mechanisms of Qi-Long-Tian formula using a rat model in a simulated plateau environment."	Dilution 1:100
Authors: Fu X,Yang C,Chen B,Zeng K,Chen S,Fu Y	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.