

# Tyrosine Hydroxylase Monoclonal Antibody (185)


Product Details	
Size	50 µL
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Mouse, Human
Host/Isotype	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	185
Conjugate	Unconjugated
Immunogen	Recombinant protein corresponding to the C-terminal portion of mouse Tyrosine Hydroxylase.
Form	Liquid
Concentration	0.24 mg/mL
Storage buffer	tissue culture supernatant
Contains	15mM sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_795666

Applications	Tested Dilution	Publications
Western Blot (WB)	1:25-1:50	-
Immunohistochemistry (IHC)	-	7 Publications
Immunohistochemistry (Paraffin) (IHC (P))	Assay-dependent	-
Immunohistochemistry (Frozen) (IHC (F))	Assay-dependent	-
Immunocytochemistry (ICC/IF)	1:50	2 Publications

## Product Specific Information


Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For Tyrosine Hydroxylase Monoclonal Antibody (185)



Tyrosine Hydroxylase Antibody (MA1-24654)

Detection of altered expression of the target protein by cell treatment demonstrates antibody specificity. Immunofluorescence analysis of Tyrosine Hydroxylase using Tyrosine Hydroxylase Monoclonal Antibody (185) (Product # MA1-24654) shows increased expression of Tyrosine Hydroxylase in PC-12 cell line upon Dexamethasone treatment at a concentration of 5 µg/mL for 6 days. {TM}




Tyrosine Hydroxylase Antibody (MA1-24654) in ICC/IF

Immunofluorescence analysis of Tyrosine Hydroxylase using Tyrosine Hydroxylase Monoclonal Antibody (185) (Product # MA1-24654) was performed using 70% confluent log phase PC-12 cells treated with 5 µg/mL dexamethasone for 6 days. The cells were fixed with 4% Paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, and blocked with 2% BSA for 10 minutes at room temperature. The cells were labeled with Tyrosine Hydroxylase Monoclonal Antibody (185) (Product # MA1-24654) at 1:50 µg/mL in 0.1% BSA, incubated at 4 degree Celsius overnight and then labeled with Goat anti-Mouse IgG (H+L), Superclonal™ Recombinant Secondary Antibody, Alexa Fluor 488 (Product # A28175), (1:2000 dilution) for 45 minutes at room temperature (Panel a: Green). Nuclei (Panel b: Blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: Red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing Cytoplasmic localization. Panel e represents untreated PC-12 cells having low expression of TH. Panel f represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.

Tyrosine Hydroxylase Antibody (MA1-24654)

Altered expression of Tyrosine Hydroxylase protein upon cell treatment demonstrated antibody specificity. There was a treatment mediated increase in the expression of Tyrosine Hydroxylase in PC-12 cells upon dexamethasone treatment. {TM}



View more figures on [thermofisher.com](https://thermofisher.com)

## Immunohistochemistry (7)

<p><b>Frontiers in synaptic neuroscience</b></p> <p><b>Somatostatin Neurons in the Mouse Pontine Nucleus Activate GABA<sub>A</sub> Receptor Mediated Synaptic Currents in Locus Coeruleus Neurons.</b></p> <p>"MA1-24654 was used in Immunohistochemistry to include corticotropin-releasing factor (CRF+) expressing neurons in the BRN that control bladder contraction and somatostatin expressing (SST+) neurons whose role in this region has not been discerned."</p> <p>Authors: Garcia DuBar S,Cosio D,Korthas H, Van Batavia JP,Zderic SA,Sahibzada N,Valentino RJ,Vicini S</p>	<p><b>Year</b> 2022</p> <p><b>Species</b> Mouse</p> <p><b>Dilution</b> 1:200</p>
<p><b>Molecular and cellular biology</b></p> <p><b>Membrane Trafficking Protein CDP138 Regulates Fat Browning and Insulin Sensitivity through Controlling Catecholamine Release.</b></p> <p>"MA1-24654 was used in Immunohistochemistry to report that mice without CDP138 develop obesity under normal chow diet (NCD) or high-fat diet (HFD) conditions."</p> <p>Authors: Zhou QL,Song Y,Huang CH,Huang JY,Gong Z,Liao Z,Sharma AG,Green L,Deng JZ,Rigor MC,Xie X,Qi S,Ayala JE,Jiang ZY</p>	<p><b>Year</b> 2018</p> <p><b>Species</b> Mouse</p> <p><b>Dilution</b> 1:80</p>

[View more IHC references on thermofisher.com](#)

## Immunocytochemistry (2)

<p><b>Cellular and molecular gastroenterology and hepatology</b></p> <p><b>Lack of Mucosal Cholinergic Innervation Is Associated With Increased Risk of Enterocolitis in Hirschsprung's Disease.</b></p> <p>"MA1-24654 was used in Immunocytochemistry to study the impact of cholinergic signals Hirschsprung's disease - associated enterocolitis."</p> <p>Authors: Keck S,Galati-Fournier V,Kym U,Moesch M,Usemann J,Müller I,Subotic U,Tharakan SJ,Krebs T,Stathopoulos E,Schmittenebecher P,Cholewa D,Romero P,Reingruber B,Bruder E,Group NS,Holland-Cunz S</p>	<p><b>Year</b> 2022</p> <p><b>Species</b> Human</p>
<p><b>ASN neuro</b></p> <p><b>Restoration of Noradrenergic Function in Parkinson's Disease Model Mice.</b></p> <p>"Published figure using Tyrosine Hydroxylase monoclonal antibody (Product # MA1-24654) in Immunocytochemistry"</p> <p>Authors: Cui K,Yang F,Tufan T,Raza MU,Zhan Y,Fan Y,Zeng F,Brown RW,Price JB,Jones TC,Miller GW,Zhu MY</p>	<p><b>Year</b> 2021</p>

## More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.