

HIF1A Monoclonal Antibody (mgc3)

Product Details

| | |
|--------------------|--|
| Size | 100 µL |
| Species Reactivity | Bovine, Human, Mouse, Non-human primate, Pig |
| Published Species | Rabbit, Rat, Bovine, Human, Mouse |
| Host/Isotype | Mouse / IgG1 |
| Class | Monoclonal |
| Type | Antibody |
| Clone | mgc3 |
| Conjugate | Unconjugated |
| Immunogen | Human HIF-1 alpha amino acids 530-826. |
| Form | Liquid |
| Concentration | 1 mg/mL |
| Purification | Protein A |
| Storage buffer | PBS, pH 7.4, with 1mg/mL BSA |
| Contains | 0.05% sodium azide |
| Storage conditions | -20° C, Avoid Freeze/Thaw Cycles |
| RRID | AB_325431 |

| Applications | Tested Dilution | Publications |
|---|-----------------|-----------------|
| Western Blot (WB) | 1:2,000 | 17 Publications |
| Immunohistochemistry (IHC) | - | 7 Publications |
| Immunohistochemistry (Paraffin) (IHC (P)) | 1:10-1:100 | - |
| Immunocytochemistry (ICC/IF) | 1:20-1:200 | 3 Publications |
| Flow Cytometry (Flow) | - | 1 Publication |
| Immunoprecipitation (IP) | Assay-dependent | - |
| Neutralization (Neu) | - | 1 Publication |
| Gel Shift (GS) | Assay-dependent | 1 Publication |
| Immunoelectrophoresis (IE) | Assay-dependent | - |

Product Specific Information

MA1-516 detects hypoxia-inducible factor 1 alpha (HIF-1 alpha) from human, non-human primate, bovine, mouse and porcine cells. This antibody does not cross-react with ARNT or the related HIF-2 alpha.

MA1-516 has been successfully used in Western blot, immunofluorescence, immunoprecipitation, immunocytochemistry, and gel shift procedures. By Western blot, this antibody detects an ~116 kDa protein representing HIF-1 alpha after hypoxic induction in COS cells. Immunofluorescence staining of HIF-1 alpha in COS-7 cells with MA1-516 yields nuclear staining after exposing cells to 1% oxygen for 4 hours. In gel shift assays, MA1-516 has been successfully used only with mouse HIF-1 alpha.


Antibodies to this protein (and modification) were previously sold as part of a Thermo Scientific Cellomics High Content Screening Kit. This replacement antibody is now recommended for researchers who need an antibody for high content cell based assays. It has been thoroughly tested and validated for cellular immunofluorescence (IF) applications. Further

optimization including the selection of the most appropriate fluorescent Dylight conjugated secondary antibody may have to be performed for your high content assay.

Product Images For HIF1A Monoclonal Antibody (mgc3)


HIF1A Antibody (MA1-516) in ICC/IF

Immunofluorescent analysis of HIF-1 alpha (green) in HeLa cells either left untreated (left panel) or treated with 100uM Deferoxamine mesylate for ~16 hours (right panel). Formalin-fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 15 minutes at room temperature and blocked with 0.3% BSA for 15 minutes at room temperature. Cells were probed with a HIF-1 alpha monoclonal antibody (Product # MA1-516) at a dilution of 1:100 for at least 1 hour at room temperature, washed with PBS, and incubated with a DyLight 488-conjugated goat anti-mouse IgG secondary antibody (Product # 35502) at a dilution of 1:500 for 30 minutes at room temperature. F-actin (red) was stained with DyLight 594 Phalloidin (Product # 21836) and nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Images were taken on a Thermo Scientific ArrayScan Instrument at 20X magnification.




HIF1A Antibody (MA1-516)

The specificity of anti-HIF1-alpha antibody (Product # MA1-516) was demonstrated by the immunofluorescence detection of increased accumulation of HIF1-alpha in the nucleus in A549 cells upon treatment with deferoxamine mesylate (right panel) compared to untreated cells (left panel). {TM}



HIF1A Antibody (MA1-516)

The specificity of anti-HIF1-alpha antibody (Product # MA1-516) was demonstrated by the immunofluorescence detection of increased accumulation of HIF1-alpha in the nucleus in HeLa cells upon treatment with deferoxamine mesylate (right panel) compared to untreated cells (left panel). {TM}



View more figures on thermofisher.com

Western Blot (17)

| | |
|--|--------------------|
| Life (Basel, Switzerland) | Year 2023 |
| Low-Level Laser Therapy Induces Melanoma Tumor Growth by Promoting Angiogenesis. | Species Mouse |
| "Published figure using HIF1A monoclonal antibody (Product # MA1-516) in Western Blot" | |
| Authors: Lin YY, Lee SY, Cheng YJ | |
| Oncology reports | Year 2023 |
| Activating transcription factor 4 regulates hypoxia inducible factor 1 in chronic hypoxia in pancreatic cancer cells. | Species Human |
| "Published figure using HIF1A monoclonal antibody (Product # MA1-516) in Western Blot" | Dilution 1:1000 |
| Authors: Chee NT, Carriere CH, Miller Z, Welford S, Brothers SP | |

View more WB references on thermofisher.com

Immunohistochemistry (7)

| | |
|---|------------------|
| Frontiers in immunology | Year 2022 |
| IL-17 Induces Autophagy Dysfunction to Promote Inflammatory Cell Death and Fibrosis in Keloid Fibroblasts <i>via</i> the STAT3 and HIF-1 Dependent Signaling Pathways. | |
| "Published figure using HIF1A monoclonal antibody (Product # MA1-516) in Immunohistochemistry" | |
| Authors: Lee SY, Lee AR, Choi JW, Lee CR, Cho KH, Lee JH, Cho ML | |
| Frontiers in oncology | Year 2020 |
| An Integrated Score and Nomogram Combining Clinical and Immunohistochemistry Factors to Predict High ISUP Grade Clear Cell Renal Cell Carcinoma. | Species Human |
| "MA1-516 was used in Immunohistochemistry to combine clinical and immunohistochemical factors for the prediction of high ISUP grade clear cell renal cell carcinoma in an attempt to improve the accuracy of a biopsy-based diagnosis." | |
| Authors: Wu J, Xu WH, Wei Y, Qu YY, Zhang HL, Ye DW | |

View more IHC references on thermofisher.com

More applications with references on thermofisher.com

- ICC/IF (3)
- Flow (1)
- Neu (1)
- GS (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.