

# HSP70 Monoclonal Antibody (5A5)

## Product Details

Size	250 µL
Species Reactivity	Amphibian, Avian, Dog, Fruit fly, Fish, Flatworm, Human, Mouse, Non-human primate, Rat, Yeast
Published Species	Rabbit, Yeast, Rat, Fruit fly, Mollusc, Amphibian, Bovine, Human, Mouse
Host/Isotope	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	5A5
Conjugate	Unconjugated
Immunogen	Human recombinant HSP70 over expressed in E. coli.
Form	Liquid
Concentration	1.0 mg/mL
Purification	Protein A
Storage buffer	PBS with 1mg/mL BSA
Contains	0.05% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_325455

Applications	Tested	Dilution	Published
Western Blot (WB)	✓	1:250 - 1:1000	29 Publications
ELISA (ELISA)	-	1:1000	2 Publications
Immunocytochemistry (ICC)	✓	1:200	2 Publications
Immunohistochemistry (IHC)	-	1:200	4 Publications
Immunofluorescence (IF)	✓	1:200	1 Publication
Immunoprecipitation (IP)	✓	Assay Dependent	1 Publication
Gel Shift (GS)	✓	Assay Dependent	1 Publication
Neutralization (Neu)	-		1 Publication
Immunohistochemistry (Frozen) (IHC (F))	✓	Assay Dependent	

## Product Specific Information

MA3-007 detects several members of the heat shock protein 70 kDa (HSP70) gene family including HSP70, HSC70, GRP78, and following heat shock, HSP72 from yeast, rat, Drosophila, fish, mouse, avian, amphibian and human samples.

MA3-007 has been successfully used in Western blot, immunofluorescence, gel shift, immunohistochemistry (frozen), and immunoprecipitation procedures. By Western blot, this antibody detects proteins from ~70 kDa to ~78 kDa representing different members of the HSP70 family. 2-dimensional gel electrophoresis is required to resolve the heat induced form of these proteins from their constitutively expressed counterparts. Immunofluorescence staining of HSP70 in heat shocked HeLa cells with MA3-007


results in cytoplasmic staining.

The MA3-007 antigen is recombinant human HSP70 over-expressed in E. coli. Epitope mapping with a panel of HSP70 deletion mutants suggests that the epitope recognized is located between amino acids 122-264 of human HSP70, a region that has been shown to be involved in ATP binding. This is the first monoclonal antibody reported to react with: 1) the ATP binding region of HSP70, 2) an epitope in the amino terminus of HSP70.

## Advanced Verification Data

### HSP70 Antibody (MA3-007)


Altered expression of proteins upon cell treatment demonstrates antibody specificity. Western blot using HSP70 Mouse Monoclonal Antibody (5A5) (Product # MA3-007), shows increased expression of proteins upon heat shock treatment. Cell Treatment validation info.



## Product Images For HSP70 Monoclonal Antibody (5A5)


### HSP70 Antibody (MA3-007) in IF

Immunofluorescence analysis of HSP70 was performed using 70% confluent log phase HEK-293 cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 15 minutes, and blocked with 2% BSA for 1 hour at room temperature. The cells were labeled with HSP70 Monoclonal Antibody (5A5) (Product # MA3-007) at 1:200 dilution in 0.1% BSA, incubated at 4 degree Celsius overnight and then labeled with Goat anti-Mouse IgG (H+L), Superclonal™ Recombinant Secondary Antibody, Alexa Fluor 488 conjugate (Product # A28175) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing localization to nucleus and cytoplasm. Panel e represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.



### HSP70 Antibody (MA3-007) in IF

Immunofluorescent analysis of Heat Shock Protein 70 (HSP70) (green) in HeLa and NIH3T3 cells. Formalin fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 10 minutes at room temperature and blocked with 1% Blocker BSA (Product # 37525) for 15 minutes at room temperature. Cells were probed with a HSP70 Monoclonal Antibody (Product # MA3-007), at a dilution of 1:50 for at least 1 hour at room temperature, washed with PBS, and incubated with DyLight 488 goat-anti-mouse IgG secondary antibody (Product # 35502) at a dilution of 1:400 for 30 minutes at room temperature. Nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Images were taken on a Thermo Scientific ArrayScan at 20X magnification.



[View more figures on thermofisher.com](https://www.thermofisher.com)

## 41 References

### Western Blot (29)

PloS one

#### Exosomes Derived from Squamous Head and Neck Cancer Promote Cell Survival after Ionizing Radiation.

"MA3-007 was used in western blot to calculate how ionizing radiation can promote cell survival in exosomes derived from squamous head and neck cancer"

Authors: Mutschelknaus L, Peters C, Winkler K, Yentrapalli R, Heider T, Atkinson MJ, Moertl S

**Species**  
Human  
Not Applicable

**Dilution**  
Not Cited  
Not Cited

**Year**  
2016

The Journal of experimental biology

#### Intermittent hypoxia leads to functional reorganization of mitochondria and affects cellular bioenergetics in marine molluscs.

"MA3-007 was used in western blot to determine the affect of cellular bioenergetics in marine molluscs and functional reorganization of mitochondria by intermittent hypoxia"

Authors: Ivanina AV, Nesmelova I, Leamy L, Sokolov EP, Sokolova IM

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2016

[View more WB references on thermofisher.com](#)

### ELISA (2)

Journal of evolutionary biology

#### Hsp70 protein levels and thermotolerance in Drosophila subobscura: a reassessment of the thermal co-adaptation hypothesis.

"MA3-007 was used in ELISA to test the thermal co-adaptation hypothesis using Drosophila subobscura"

Authors: Calabria G, Dolgova O, Rego C, Castañeda LE, Rezende EL, Balanyà J, Pascual M, Sørensen JG, Loeschcke V, Santos M

**Species**  
Fruit fly

**Dilution**  
1:1000

**Year**  
2012

Oecologia

#### Assay conditions in laboratory experiments: is the use of constant rather than fluctuating temperatures justified when investigating temperature-induced plasticity?

"MA3007 was used in ELISA to evaluate if the use of constant temperatures is justified when studying Lycaena tityrus"

Authors: Fischer K, Kölzow N, Höltje H, Karl I

**Species**  
Not Applicable

**Dilution**  
1:700

**Year**  
2011

### More applications with references on thermofisher.com

ICC (2)

IHC (4)

IF (1)

IP (1)

GS (1)

Neu (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.