

Lamin A/C Monoclonal Antibody (mab636)

Product Details	
Size	200 µL
Species Reactivity	Bovine, Human, Pig
Published Species	Artificial Control, Human
Host/Isotype	Mouse / IgG2b
Class	Monoclonal
Type	Antibody
Clone	mab636
Conjugate	Unconjugated
Immunogen	Porcine lamin preparation.
Form	Liquid
Concentration	Conc. Not Determined
Storage buffer	tissue culture supernatant
Contains	0.05% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_325377

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC)	1:100	4 Publications
Immunofluorescence (IF)	1:100	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	1:100	-
Western Blot (WB)	1:100 - 1:2000	10 Publications

Product Specific Information


MA3-1000 detects lamin A/C from human, bovine, porcine and canine samples.

MA3-1000 has been successfully used in Western blot, immunofluorescence and immunohistochemistry procedures. By Western blot, this antibody detects ~ 70 and 65 kDa proteins corresponding to lamin A and C, respectively, from HeLa cell extract. This antibody can also be used for immunofluorescence and immunohistochemistry for subcellular localization experiments. MA3-1000 has been widely used for detection of lamin A/C control in siRNA experiments.

The MA3-1000 antigen is porcine lamin preparation.


Product Images For Lamin A/C Monoclonal Antibody (mab636)

Lamin A/C Antibody (MA3-1000) in IF




Immunofluorescent analysis of Lamin A/C (green) in untreated U2-OS cells (A) or HeLa cells (B). Formalin fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 10 minutes at room temperature. Cells were then blocked with 0.3% BSA for 15 minutes at room temperature. Cells were then probed with a mouse monoclonal antibody recognizing Lamin A/C (Product # MA3-1000), at a dilution of 1:100 for at least 1 hour at room temperature. Cells were then washed with PBS and incubated with DyLight 488 goat-anti-mouse secondary antibody (Product # 35503) at a dilution of 1:400 for 30 minutes at room temperature. Nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Images were taken on a Thermo Scientific ArrayScan at 20X magnification.

Lamin A/C Antibody (MA3-1000) in IF



Immunofluorescent analysis of Lamin A/C (red) in MDCK cells. The cells were permeabilized with 0.1% Triton X-100 in PBS for 15 minutes, and blocked with 3% BSA in PBS (Product # 37525) for 15 minutes at room temperature. Cells were stained with a Lamin A/C mouse monoclonal antibody (Product # MA3-1000), at a dilution 1:100 in blocking buffer for at least 1 hour at room temperature, and then incubated with a Rabbit anti-Mouse IgG (H+L) Superclonal™ Secondary Antibody, Alexa Fluor® 594 conjugate (Product # A27027) at a dilution of 1:1000 for 30 minutes at room temperature (red). Nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Images were taken on a Thermo Scientific ToxInsight Instrument at 20X magnification.



Lamin A/C Antibody (MA3-1000) in IF

Immunofluorescent analysis of Lamin A/C using Lamin A/C Monoclonal Antibody (mab636) (Product # MA3-1000) shows staining in U251 Cells. Lamin A/C (green), F-Actin staining with Phalloidin (red) and nuclei with DAPI (blue) is shown. Cells were grown on chamber slides and fixed with formaldehyde prior to staining. Cells were probed without (control) or with an antibody recognizing Lamin A/C (Product # MA3-1000) at a dilution of 1:200 overnight at 4 °C, washed with PBS and incubated with a DyLight-488 conjugated secondary antibody (Product # 35552 for GAR, Product # 35503 for GAM). Images were taken at 60X magnification.

[View more figures on thermofisher.com](http://thermofisher.com)

16 References

Western Blot (10)

Journal of virology

Human Cytomegalovirus pUL93 Links Nucleocapsid Maturation and Nuclear Egress.

"MA3-1000 was used in western blot to determine the link between nuclear egress and nucleocapsid maturation by human cytomegalovirus pUL93"

Authors: DeRussy BM,Boland MT,Tandon R

Species
Not Applicable

Dilution
Not Cited

Year
2016

Disease markers

Placental Expression of NEMO Protein in Normal Pregnancy and Preeclampsia.

"MA3-1000 was used in Western Blotting to examine the level and localisation of the NEMO protein in preeclamptic and nonpreeclamptic placentas."

Authors: Sakowicz A,Lisowska M,Biesiada L,Puciennik E,Gach A,Rybak-Krzyszowska M,Huras H,Sakowicz B,Romanowicz H,Piastowska-Ciesielska AW,Grzesiak M,Pietrucha T

Species
Human

Dilution
1:500

Year
2019

[View more WB references on thermofisher.com](#)

Immunocytochemistry (4)

Journal of drug design and research

Exploring Modifications of an HIV-1 Capsid Inhibitor: Design, Synthesis, and Mechanism of Action.

"MA3-1000 was used in Immunocytochemistry-immunofluorescence to investigate bioisosteric modification of the the HIV-1 capsid inhibitor PF-3450074 scaffold as a first step in redeveloping this compound."

Authors: Xu JP,Francis AC,Meuser ME,Mankowski M,Ptak RG,Rashad AA,Melikyan GB,Cocklin S

Species
Human

Dilution
Not Cited

Year
2020

Cells

Inhibition of JAK-STAT Signaling with Baricitinib Reduces Inflammation and Improves Cellular Homeostasis in Progeria Cells.

"MA3-1000 was used in Immunocytochemistry to report that the inhibition of the JAK-STAT pathway with baricitinib, a Food and Drug Administration-approved JAK1/2 inhibitor, restored cellular homeostasis, delayed senescence and decreased proinflammatory markers in HGPS cells."

Authors: Liu C,Arnold R,Henriques G,Djabali K

Species
Human

Dilution
Not Cited

Year
2019

[View more ICC references on thermofisher.com](#)

More applications with references on thermofisher.com

IF (2)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.