

SERCA1 ATPase Monoclonal Antibody (IIH11)

Product Details

Size	100 µL
Species Reactivity	Dog, Guinea pig, Human, Mouse, Rabbit, Rat
Published Species	Dog, Rabbit, Rat, Human, Mouse, Invertebrate
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	IIH11
Conjugate	Unconjugated
Immunogen	Purified rabbit skeletal muscle sarcoplasmic reticulum.
Form	Liquid
Concentration	Conc. Not Determined
Storage buffer	PBS, ascites
Contains	0.05% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_325494

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:5,000	60 Publications
Immunohistochemistry (IHC)	-	16 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:20-1:200	-
Immunohistochemistry (Frozen) (IHC (F))	1:20-1:200	-
Immunocytochemistry (ICC/IF)	1:500	2 Publications


Product Specific Information

MA3-911 detects sarcoplasmic or endoplasmic reticulum calcium 1 (SERCA1) ATPase from canine, human, rabbit, rat, mouse and guinea pig tissues.

MA3-911 has been successfully used in Western blot, immunohistochemistry, and immunofluorescence procedures. By Western blot, this antibody detects an ~110 kDa protein representing SERCA1 ATPase in canine skeletal muscle extracts. Immunofluorescence staining of SERCA1 ATPase in canine skeletal muscle with MA3-911 results in strong labeling of the entire type II (fast) myofiber.


The MA3-911 antigen is purified rabbit skeletal muscle sarcoplasmic reticulum. This antibody recognizes an epitope between amino acids 199-505 of rabbit skeletal muscle ATPase, a region that is not exposed in native sarcoplasmic reticulum.

Product Images For SERCA1 ATPase Monoclonal Antibody (IIH11)




SERCA1 ATPase Antibody (MA3-911) in ICC/IF

Immunofluorescent analysis of SERCA1 ATPase using Anti-SERCA1 ATPase Monoclonal Antibody (IIH11) (Product # MA3-911) shows staining in C6 Cells. SERCA1 ATPase staining (green), F-Actin staining with Phalloidin (red) and nuclei with DAPI (blue) is shown. Cells were grown on chamber slides and fixed with formaldehyde prior to staining. Cells were probed without (control) or with or an antibody recognizing SERCA1 ATPase (Product # MA3-911) at a dilution of 1: 200 over night at 4°C, washed with PBS and incubated with a DyLight-488 conjugated secondary antibody (Product # 35503, Goat Anti-Mouse). Images were taken at 60X magnification.



SERCA1 ATPase Antibody (MA3-911) in IHC (P)

Immunohistochemistry was performed on normal biopsies of deparaffinized Mouse skeletal muscle tissue. To expose target proteins, heat induced antigen retrieval was performed using 10mM sodium citrate (pH6.0) buffer, microwaved for 8-15 minutes. Following antigen retrieval tissues were blocked in 3% BSA-PBS for 30 minutes at room temperature. Tissues were then probed at a dilution of 1:200 with a mouse monoclonal antibody recognizing SERCA1 ATPase (Product # MA3-911) or without primary antibody (negative control) overnight at 4°C in a humidified chamber. Tissues were washed extensively with PBST and endogenous peroxidase activity was quenched with a peroxidase suppressor. Detection was performed using a biotin-conjugated secondary antibody and SA-HRP, followed by colorimetric detection using DAB. Tissues were counterstained with hematoxylin and prepped for mounting.



SERCA1 ATPase Antibody (MA3-911) in IHC (P)

Immunohistochemistry was performed on normal biopsies of deparaffinized Mouse lymph node tissue. To expose target proteins, heat induced antigen retrieval was performed using 10mM sodium citrate (pH6.0) buffer, microwaved for 8-15 minutes. Following antigen retrieval tissues were blocked in 3% BSA-PBS for 30 minutes at room temperature. Tissues were then probed at a dilution of 1:200 with a mouse monoclonal antibody recognizing SERCA1 ATPase (Product # MA3-911) or without primary antibody (negative control) overnight at 4°C in a humidified chamber. Tissues were washed extensively with PBST and endogenous peroxidase activity was quenched with a peroxidase suppressor. Detection was performed using a biotin-conjugated secondary antibody and SA-HRP, followed by colorimetric detection using DAB. Tissues were counterstained with hematoxylin and prepped for mounting.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Western Blot (60)

FEBS letters

Neuronatin promotes SERCA uncoupling and its expression is altered in skeletal muscles of high-fat diet-fed mice.

"MA3-911 was used in Immunocytochemistry, Immunohistochemistry (Frozen), Western Blot to examine whether neuronatin could uncouple the Ca²⁺ transport activity of sarco(endo)plasmic reticulum Ca²⁺ -ATPase from ATP hydrolysis, similarly to sarcolipin."

Authors: Braun JL,Teng ACT,Geromella MS,Ryan CR,Fenech RK,MacPherson REK,Gramolini AO,Fajardo VA

Year
2021

Species
Human

Dilution
1:5000

Frontiers in physiology

Electrical Stimulation Prevents Preferential Skeletal Muscle Myosin Loss in Steroid-Denervation Rats.

"MA3-911 was used in Western Blotting to demonstrate that electrical stimulation treatment is an effective way to prevent muscle impairments associated with loss of myosin."

Authors: Yamada T,Himori K,Tatebayashi D,Yamada R,Ashida Y,Imai T,Akatsuka M,Masuda Y,Kanzaki K,Watanabe D,Wada M,Westerblad H,Lanner JT

Year
2020

Species
Rat

[View more WB references on thermofisher.com](#)

Immunohistochemistry (16)

Acta neuropathologica communications

Nebulin nemaline myopathy recapitulated in a compound heterozygous mouse model with both a missense and a nonsense mutation in Neb.

"MA3-911 was used in Immunohistochemistry to characterise a mouse strain with compound heterozygous Neb mutations; one missense (p.Tyr2303His), affecting a conserved actin-binding site and one nonsense mutation (p. Tyr935*), introducing a premature stop codon early in the protein."

Authors: Laitila JM,McNamara EL,Wingate CD,Goulee H,Ross JA,Taylor RL,van der Pijl R,Griffiths LM,Harries R,Ravenscroft G,Clayton JS,Sewry C,Lawlor MW,Ottenheijm CAC,Bakker AJ,Ochala J,Laing NG,Wallgren-Pettersson C,Pelin K,Nowak KJ

Year
2020

Species
Mouse

Dilution
1:1000

International journal of experimental pathology

Primary over-expression of APP in muscle does not lead to the development of inclusion body myositis in a new lineage of the MCK-APP transgenic mouse.

"MA3-911 was used in immunohistochemistry to study the lack of inclusion body myositis resulting from skeletal muscle AbetaPP overexpression in a novel lineage of the MCK-AbetaPP transgenic mouse"

Authors: Luo YB,Johnsen RD,Griffiths L,Needham M,Fabian VA,Fletcher S,Wilton SD,Mastaglia FL

Year
2013

Species
Mouse

Dilution
1:15

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

ICC/IF (2)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.