

# CD44 Monoclonal Antibody (1M7.8.1)

Product Details	
Size	500 µg
Species Reactivity	Human, Mouse
Published Species	Rat, Mouse
Host/Isotope	Rat / IgG2b
Class	Monoclonal
Type	Antibody
Clone	1M7.8.1
Conjugate	Unconjugated
Immunogen	Mouse 80-95 kD lymphocyte surface glycoprotein H-CAM (CD44).
Form	Liquid
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	PBS
Contains	no preservative
Storage Conditions	-20°C
RRID	AB_223593

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	Assay Dependent	4 Publications
Immunocytochemistry (ICC)	1:10-1:100	1 Publication
Immunofluorescence (IF)	1:10-1:100	-
Immunoprecipitation (IP)	Assay Dependent	-
Inhibition Assays (IA)	Assay Dependent	-
Western Blot (WB)	Assay Dependent	-
Miscellaneous PubMed (Misc)	-	1 Publication

## Product Specific Information

MA4405 targets CD44 in FACS, IA, IF, IP, and WB applications and shows reactivity with mouse and Human samples.

The MA4405 immunogen is mouse 80-95 kD lymphocyte surface glycoprotein H-CAM (CD44).


MA4405 detects a standard 85-kDa isoform of CD44 and a number of high molecular mass variant isoforms.

This antibody is produced by injecting Rat IgG secreting hybridoma cells into the peritoneum of mice. The resulting ascites is collected from the mice and the antibody is purified.

This product is a Low Endotoxin formulation.


This product has been tested for endotoxins by limulus amoebocyte lysate (LAL) assay and contains an endotoxin concentration of less than or equal to 10 endotoxin units per milligram (EU/mg).

## Product Images For CD44 Monoclonal Antibody (1M7.8.1)




### CD44 Antibody (MA4405) in IF

Immunofluorescent analysis of CD44 (green) showing staining in the membrane and cytoplasm of NIH-3T3 cells (right) compared to a negative control without primary antibody (left). Formalin-fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 5-10 minutes and blocked with 3% BSA-PBS for 30 minutes at room temperature. Cells were probed with a CD44 monoclonal antibody (Product # MA4405) in 3% BSA-PBS at a dilution of 1:20 and incubated overnight at 4°C in a humidified chamber. Cells were washed with PBST and incubated with a DyLight-conjugated secondary antibody in PBS at room temperature in the dark. F-actin (red) was stained with a fluorescent red phalloidin and nuclei (blue) were stained with Hoechst or DAPI. Images were taken at a magnification of 60x.



### CD44 Antibody (MA4405) in IF

Immunofluorescent analysis of CD44 (green) showing staining in the membrane of BAF-3 cells (right) compared to a negative control without primary antibody (left). Formalin-fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 5-10 minutes and blocked with 3% BSA-PBS for 30 minutes at room temperature. Cells were probed with a CD44 monoclonal antibody (Product # MA4405) in 3% BSA-PBS at a dilution of 1:20 and incubated overnight at 4°C in a humidified chamber. Cells were washed with PBST and incubated with a DyLight-conjugated secondary antibody in PBS at room temperature in the dark. F-actin (red) was stained with a fluorescent red phalloidin and nuclei (blue) were stained with Hoechst or DAPI. Images were taken at a magnification of 60x.



### CD44 Antibody (MA4405) in IF

Immunofluorescent analysis of CD44 (green) showing staining in the membrane of HeLa cells (right) compared to a negative control without primary antibody (left). Formalin-fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 5-10 minutes and blocked with 3% BSA-PBS for 30 minutes at room temperature. Cells were probed with a CD44 monoclonal antibody (Product # MA4405) in 3% BSA-PBS at a dilution of 1:20 and incubated overnight at 4°C in a humidified chamber. Cells were washed with PBST and incubated with a DyLight-conjugated secondary antibody in PBS at room temperature in the dark. F-actin (red) was stained with a fluorescent red phalloidin and nuclei (blue) were stained with Hoechst or DAPI. Images were taken at a magnification of 60x.

[View more figures on thermofisher.com](https://www.thermofisher.com)

## Flow Cytometry (4)

The Journal of experimental medicine

### DOCK8 deficiency impairs CD8 T cell survival and function in humans and mice.

"MA4405 was used in flow cytometry to determine the role for DOCK8 in peripheral CD8 T cell survival and function"

Authors: Randall KL, Chan SS, Ma CS, Fung I, Mei Y, Yabas M, Tan A, Arkwright PD, Al Suwairi W, Lugo Reyes SO, Yamazaki-Nakashimada MA, Garcia-Cruz Mde L, Smart JM, Picard C, Okada S, Jouanguy E, Casanova JL, Lambe T, Cornall RJ, Russell S, Oliaro J, Tangye SG, Bertram EM, Goodnow CC

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2011

Journal of immunology (Baltimore, Md. : 1950)

### Resistance to murine AIDS in offspring of mice infected with LP-BM5. Role of CD8 T cells.

"MA4405 was used in flow cytometry to investigate the role of CD8 T cells in immune responses against murine leukemia viruses"

Authors: Pavlovitch JH, Hulier E, Rizk-Rabin M, Marussig M, Mazier D, Joffret ML, Hoos S, Papiernik M

**Species**  
Mouse

**Dilution**  
Not Cited

**Year**  
1996

[View more Flow references on thermofisher.com](#)

## Miscellaneous PubMed (1)

European journal of immunology

### Lymphoid environment limits superantigen and antigen-induced T cell proliferation at high precursor frequency.

"MA4405 was used in flow cytometry to report that the lymphoid environment limits T cell proliferation in response to high superantigen levels."

Authors: Attinger A, MacDonald HR, Acha-Orbea H

**Species**  
Mouse

**Dilution**  
Not Cited

**Year**  
2001

## Immunocytochemistry (1)

Immunogenetics

### Genetic characterization of a polymorphic murine cell-surface glycoprotein.

"MA4405 was used in immunocytochemistry to characterize a murine cell-surface glycoprotein Pgp-1"

Authors: Lesley J, Trowbridge IS

**Species**  
Rat

**Dilution**  
Not Cited

**Year**  
1982

## More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.