

Ly-6G Monoclonal Antibody (1A8-Ly6g), Super Bright™ 702, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), Super Bright™ 702, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	1A8-Ly6g
Conjugate	Super Bright™ 702
Excitation/Emission Max	413/702 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2784889

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	4 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunocytochemistry (ICC/IF)	-	2 Publications
Flow Cytometry (Flow)	0.5 µg/test	18 Publications

Product Specific Information

Description: The monoclonal antibody 1A8-Ly6g reacts with mouse Ly-6G, which is also known as Gr-1. Ly-6G is a 25-kDa GPI protein expressed exclusively by neutrophils. Studies suggest an important role in neutrophil infiltration, recruitment and migration. Ly-6G associates with B2 integrins CD11a and CD11b and can attenuate B2 integrin expression and function. The ligand for Ly-6G is currently unknown.™

™ Unlike the RB6-8C5 antibody, 1A8-Ly6g is reported to only bind to Ly-6G found on neutrophils. Moreover, 1A8-Ly6g has been used to deplete neutrophils and reported to have antagonist activity.™

™ Applications Reported: This 1A8-Ly6G antibody has been reported for use in flow cytometric analysis.™

™ Applications Tested: This 1A8-Ly6G antibody has been tested by flow cytometric analysis of mouse bone marrow cells. This may be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.™

™ Super Bright 702 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 702 nm. We recommend

using a 710/50 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.™

™

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.™

™

Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.™

™

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222-49) (100 µL of cell sample + 100 µL of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333-57) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.™


™

Excitation: 405 nm; Emission: 702 nm; Laser: Violet Laser™

™

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For Ly-6G Monoclonal Antibody (1A8-Ly6g), Super Bright™ 702, eBioscience™



Ly-6G Antibody (67-9668-82) in Flow

C57BL/6 mouse bone marrow cells were stained with Ly-6C Monoclonal Antibody, APC (Product # 17-5932-82) and 0.25 µg of Rat IgG2a kappa Isotype Control, Super Bright 702 (Product # 67-4321-82) (left) or 0.25 µg of Ly-6G Monoclonal Antibody, Super Bright 702 (right). Total viable cells were used for analysis, as determined by 7-AAD (Product # 00-6993-50).

[View more figures on thermofisher.com](https://www.thermofisher.com)

25 References

Immunohistochemistry (4)

Frontiers in immunology

Interleukin-4 Programmed Macrophages Suppress Colitis and Do Not Enhance Infectious-Colitis, Inflammation-Associated Colon Cancer or Airway Hypersensitivity.

"Published figure using Ly-6G monoclonal antibody (Product # 67-9668-82) in Immunohistochemistry"

Authors: Callejas BE, Blyth GAD, Jendzjowsky N, Wang A, Babbar A, Koro K, Wilson RJA, Kelly MM, Cobo ER, McKay DM

Year
2021

NPJ Regenerative medicine

Neutrophil extracellular traps promote scar formation in post-epidural fibrosis.

"Published figure using Ly-6G monoclonal antibody (Product # 67-9668-82) in Immunohistochemistry"

Authors: Jin Z, Sun J, Song Z, Chen K, Nicolas YSM, Kc R, Ma Q, Liu J, Zhang M

Year
2020

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (Paraffin) (1)

Vaccines

CoV-RBD121-NP Vaccine Candidate Protects against Symptomatic Disease following SARS-CoV-2 Challenge in K18-hACE2 Mice and Induces Protective Responses That Prevent COVID-19-Associated Immunopathology.

"Published figure using Ly-6G monoclonal antibody (Product # 67-9668-82) in Immunocytochemistry"

Authors: DeMarco JK, Royall JM, Severson WE, Gabbard JD, Hume S, Morton J, Swope K, Simpson CA, Shepherd JW, Bratcher B, Palmer KE, Pogue GP

Year
2021

Immunocytochemistry (2)

Vaccines

CoV-RBD121-NP Vaccine Candidate Protects against Symptomatic Disease following SARS-CoV-2 Challenge in K18-hACE2 Mice and Induces Protective Responses That Prevent COVID-19-Associated Immunopathology.

"Published figure using Ly-6G monoclonal antibody (Product # 67-9668-82) in Immunocytochemistry"

Authors: DeMarco JK, Royall JM, Severson WE, Gabbard JD, Hume S, Morton J, Swope K, Simpson CA, Shepherd JW, Bratcher B, Palmer KE, Pogue GP

Year
2021

More applications with references on thermofisher.com

Flow (18)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.