

B-Raf Monoclonal Antibody (1H12F1, 1H12G10,1F12F11C9)

Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotope	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	1H12F1, 1H12G10,1F12F11C9
Conjugate	Unconjugated
Immunogen	Purified recombinant fragment of BRAF expressed in E. Coli.
Form	Liquid
Concentration	Conc. Not Determined
Storage buffer	ascites
Contains	0.03% sodium azide
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_10987001


Applications	Tested Dilution	Publications
Immunocytochemistry (ICC)	1:100	-
Immunofluorescence (IF)	1:100	-
Immunohistochemistry (IHC)	1/200 - 1/1000	-
Western Blot (WB)	1/500 - 1/2000	-

Product Specific Information

MA5-15317 targets BRAF in IHC and WB applications and shows reactivity with Human samples.


The MA5-15317 immunogen is purified recombinant fragment of BRAF expressed in E. Coli.

Advanced Verification Data



B-Raf Antibody (MA5-15317)


Antibody specificity was demonstrated by showing that antibodies raised against the same target protein perform similarly. Immunofluorescence analysis of B-Raf using B-Raf Monoclonal Antibody (Product # MA5-15317) along with another B-Raf Polyclonal Antibody (Product # PA5-14929) shows similar expression of B-Raf. Independent antibody validation info.



B-Raf Antibody (MA5-15317)

Antibody specificity was demonstrated by showing that antibodies raised against the same target protein perform similarly. Immunofluorescence analysis of B-Raf using B-Raf Monoclonal Antibody (Product # MA5-15317) along with another B-Raf Polyclonal Antibody (Product # PA5-14929) shows similar expression of B-Raf. Independent antibody validation info.

Product Images For B-Raf Monoclonal Antibody (1H12F1, 1H12G10,1F12F11C9)



B-Raf Antibody (MA5-15317) in IF

Immunofluorescence analysis of B-Raf was performed using 70% confluent log phase U-87 MG cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 15 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with B-Raf Mouse Monoclonal Antibody (Product # MA5-15317) at 1:100 dilution in 0.1% BSA, incubated at 4 degree celsius overnight and then labeled with Goat anti-Mouse IgG (H+L) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A28175) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing cytoplasmic localization. Panel e represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.

View more figures on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.