

# CD11b Monoclonal Antibody (M1/70), eFluor™ 506, eBioscience™

## Product Details

Size	100 µg
Species Reactivity	Mouse
Published Species	Fish, Mouse, Human
Host/Isotype	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), eFluor™ 506, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	M1/70
Conjugate	eFluor™ 506
Excitation/Emission Max	419/508 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2637406

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	42 Publications
Immunohistochemistry (PFA fixed) (IHC (PFA))	-	4 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications
Immunocytochemistry (ICC/IF)	-	17 Publications
Flow Cytometry (Flow)	0.125 µg/test	229 Publications
Immunoprecipitation (IP)	-	1 Publication
Neutralization (Neu)	-	2 Publications

## Product Specific Information

**Description:** The M1/70 monoclonal antibody reacts with mouse CD11b, the 165-170 kDa integrin alphaM. CD11b non-covalently associates with CD18 to form alphaM-beta2 integrin (Mac-1) and binds to CD54 (ICAM-1), C3bi, and fibrinogen. Mac-1 is expressed by macrophages, NK cells, granulocytes, activated lymphocytes and mouse B-1 cells in the peritoneal cavity. M1/70 is also cross-reactive to human CD11b, and can be used for the detection of this antigen on human peripheral blood monocytes, granulocytes, and a subset of NK cells. Through interactions with its ligands, CD11b participates in adhesive cell interactions.

**Applications Reported:** This M1/70 antibody has been reported for use in flow cytometric analysis.

**Applications Tested:** This M1/70 antibody has been tested by flow cytometric analysis of mouse bone marrow cells. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample


in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

eFluor® 506 can be excited with the violet laser line (405 nm) and emits at 506 nm. We recommend using a 510/20 band pass filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 405 nm; Emission: 506 nm; Laser: Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.

**Product Images For CD11b Monoclonal Antibody (M1/70), eFluor™ 506, eBioscience™**



**CD11b Antibody (69-0112-82) in Flow**  
Staining of C57Bl/6 bone marrow cells with Anti-Human/Mouse CD45R (B220) APC (Product # 17-0452-82) and 0.06 µg of Rat IgG2b K Isotype Control eFluor® 506 (Product # 69-4031-82) (left) or Anti-Mouse CD11b eFluor® 506 (right). Cells in the large scatter population were used for analysis.

[View more figures on thermofisher.com](#)

Immunohistochemistry (42)

<p>MedComm</p> <p><b>Single-cell transcriptomics reveals distinct cell response between acute and chronic pulmonary infection of <i>Pseudomonas aeruginosa</i>.</b></p> <p>"Published figure using CD11b monoclonal antibody (Product # 69-0112-82) in Immunohistochemistry"</p> <p>Authors: Hu X,Wu M,Ma T,Zhang Y,Zou C,Wang R,Zhang Y,Ren Y,Li Q,Liu H,Li H,Wang T,Sun X,Yang Y,Tang M,Li X, Li J,Gao X,Li T,Zhou X</p>	<p>Year</p> <p>2022</p>
<p>Journal of inflammation research</p> <p><b>Dual Activity of Ginsenoside Rb1 in Hypertrophic Cardiomyocytes and Activated Macrophages: Implications for the Therapeutic Intervention of Cardiac Hypertrophy.</b></p> <p>"Published figure using CD11b monoclonal antibody (Product # 69-0112-82) in Immunohistochemistry"</p> <p>Authors: Wang S,Cui Y,Xiong M,Li M,Wang P,Cui J,Du X,Chen Y,Zhang T</p>	<p>Year</p> <p>2022</p>

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (PFA fixed) (4)

<p>Frontiers in cardiovascular medicine</p> <p><b>Serp-1 Promotes Corneal Wound Healing by Facilitating Re-epithelialization and Inhibiting Fibrosis and Angiogenesis.</b></p> <p>"Published figure using CD11b monoclonal antibody (Product # 69-0112-82) in Immunohistochemistry (PFA fixed)"</p> <p>Authors: Ju B,Guo O,Benissan-Messan DZ,Shawver MH,Chen P,Geng B,Wei S,Yaron JR,Lucas AR,Zhu H</p>	<p>Year</p> <p>2022</p>
<p>Acta chirurgica brasileira</p> <p><b>Effect of IL-33 on pyroptosis of macrophages in mice with sepsis via NF-B/p38 MAPK signaling pathway.</b></p> <p>"Published figure using CD11b monoclonal antibody (Product # 69-0112-82) in Immunohistochemistry (PFA fixed)"</p> <p>Authors: Ke J,Cai G</p>	<p>Year</p> <p>2021</p>

[View more IHC \(PFA\) references on thermofisher.com](#)

More applications with references on thermofisher.com

- IHC (F) (2)
- ICC/IF (17)
- Flow (229)
- IP (1)
- Neu (2)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.