

PAF49 Monoclonal Antibody (GT635)

Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotype	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	GT635
Conjugate	Unconjugated
Immunogen	Recombinant fragment contains a sequence corresponding to a region within amino acids 1 and 268 of PAF49
Form	Liquid
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	PBS, pH 7
Contains	no preservative
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2538753


Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:3,000	-
Immunocytochemistry (ICC/IF)	1:100-1:1,000	-

Product Specific Information

Recommended positive controls: 293T, A431, HeLa, HepG2, A375, A549, H1299, HCT116.


Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For PAF49 Monoclonal Antibody (GT635)




PAF49 Antibody (MA5-17287) in ICC/IF

Immunofluorescent analysis of PAF49 showing staining in the nucleus of U2OS cells. U2OS cells were fixed in 4% paraformaldehyde/PBS for 15 min and stained using a PAF49 monoclonal antibody (Product # MA5-17287) diluted at 1:500. Blue: Hoechst 33342 staining.



PAF49 Antibody (MA5-17287) in WB

Western blot analysis of PAF49 using A) 30 µg 293T whole cell lysate (B) 30 µg A431 whole cell lysate (C) 30 µg HeLa whole cell lysate (D) 30 µg HepG2 whole cell lysate and E) 30 µg A375 whole cell lysate. Samples were loaded onto a 7.5% SDS-PAGE gel and probed with a PAF49 monoclonal antibody (Product # MA5-17287) at a dilution of 1:1000.



PAF49 Antibody (MA5-17287) in WB

Western Blot analysis of PAF49 was performed by separating 30 µg of various whole cell extracts by 7.5% SDS-PAGE. Proteins were transferred to a membrane and probed with a PAF49 Monoclonal Antibody (GT635) (Product # MA5-17287) at a dilution of 1:1000.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.