

CD4 Monoclonal Antibody (RPA-T4), Super Bright™ 780, eBioscience™

Product Details	
Size	25 Tests
Species Reactivity	Human
Host/Isotype	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), Super Bright™ 780, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	RPA-T4
Conjugate	Super Bright™ 780
Excitation/Emission Max	413/780 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2734980

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	2 Publications
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	12 Publications
Neutralization (Neu)	-	1 Publication

Product Specific Information

Description: The OKT4 monoclonal antibody reacts with human CD4, a 59 kDa cell surface glycoprotein expressed by the majority of thymocytes, a subpopulation of mature T cells (T-helper cells) and in low levels on monocytes. CD4 is a receptor for the human immunodeficiency virus (HIV). The OKT4 antibody recognizes a different epitope than the RPA-T4 monoclonal antibody, and these antibodies do not cross-block binding to each other's respective epitopes.

Applications Tested: This RPA-T4 antibody has been pre-diluted and tested by flow cytometric analysis of normal human peripheral blood cells. This may be used at 5 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Super Bright 780 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 780 nm. We recommend using a 780/60 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401-42) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.

In some experiments, we have observed that compensation values for Super Bright 780-conjugated antibodies are higher in the violet 450/50 channel when using UltraComp eBeads microspheres (Product # 01-2222-42) as compared to single-color stained cells. In such circumstances, we would recommend setting compensation with cells. We have also observed this in some experiments using AbC Total Antibody Compensation beads (Product # A10497).


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 μ L of cell sample + 100 μ L of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 405 nm; **Emission:** 780 nm; **Laser:** Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD4 Monoclonal Antibody (RPA-T4), Super Bright™ 780, eBioscience™



CD4 Antibody (78-0049-41) in Flow

Normal human peripheral blood cells were stained with CD3 Monoclonal Antibody, APC (Product # 17-0038-42) and Mouse IgG1 kappa Isotype Control, Super Bright 780 (Product # 78-4714-82) (left) or CD4 Monoclonal Antibody, Super Bright 780 (right). Cells in the lymphocyte gate were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

15 References

Immunohistochemistry (2)

Cells

Induced Human Regulatory T Cells Express the Glucagon-like Peptide-1 Receptor.

"Published figure using CD4 monoclonal antibody (Product # 78-0049-42) in Immunohistochemistry"

Authors: Rode AKO,Buus TB,Mraz V,Al-Jaberi FAH,Lopez DV,Ford SL,Hennen S,Eliassen IP,Klewe IV,Gharehdaghi L, Dragan A,Rosenkilde MM,Woetmann A,Skov L,Ødum N,Bonefeld CM,Kongsbak-Wismann M,Geisler C

Year
2022

JCI insight

CXCL13-producing TFH cells link immune suppression and adaptive memory in human breast cancer.

"Published figure using CD4 monoclonal antibody (Product # 78-0049-42) in Immunohistochemistry"

Authors: Gu-Trantien C,Migliori E,Buisseret L,de Wind A,Brohée S,Garaud S,Noël G,Dang Chi VL,Lodewyckx JN, Naveaux C,Duvillier H,Goriely S,Larsimont D,Willard-Gallo K

Year
2017

Flow Cytometry (12)

JCI insight

Rapamycin improves Graves' orbitopathy by suppressing CD4+ cytotoxic T lymphocytes.

"Published figure using CD4 monoclonal antibody (Product # 78-0049-42) in Flow Cytometry"

Authors: Zhang M,Chong KK,Chen ZY,Guo H,Liu YF,Kang YY,Li YJ,Shi TT,Lai KK,He MQ,Ye K,Kahaly GJ,Shi BY, Wang Y

Year
2023

Frontiers in immunology

Single-cell RNA sequencing reveals the molecular features of peripheral blood immune cells in children, adults and centenarians.

"Published figure using CD4 monoclonal antibody (Product # 78-0049-42) in Flow Cytometry"

Authors: Zhong J,Ding R,Jiang H,Li L,Wan J,Feng X,Chen M,Peng L,Li X,Lin J,Yang H,Wang M,Li Q,Chen Q

Year
2023

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

Neu (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.