

CD117 (c-Kit) Monoclonal Antibody (2B8), Super Bright™ 780, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse, Pig
Host/Isotype	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), Super Bright™ 780, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	2B8
Conjugate	Super Bright™ 780
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2734864

Applications	Tested Dilution	Publications
Western Blot (WB)	-	1 Publication
Immunocytochemistry (ICC/IF)	-	1 Publication
Flow Cytometry (Flow)	0.125 µg/test	14 Publications

Product Specific Information

Description: The 2B8 monoclonal antibody reacts with mouse CD117, also known as c-Kit receptor, Steel factor receptor, and stem cell factor receptor. A member of the tyrosine kinase receptor family, this 145-kDa molecule is expressed by a majority of hematopoietic progenitor cells characterized in the mouse bone marrow as a small subset of cells positive for Sca-1 and Thy1 (Thy1 low) and negative for lineage markers. The interaction of the mouse c-Kit receptor and steel factor promotes the proliferation and differentiation of hematopoietic progenitor cells. CD117 is also expressed by mast cells and plays a role in signaling and activation of these cells.

Applications Reported: This 2B8 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This 2B8 antibody has been tested by flow cytometric analysis of mouse bone marrow cells. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Super Bright 780 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 780 nm. We recommend using a 780/60 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.

In some experiments, we have observed that compensation values for Super Bright 780-conjugated antibodies are higher in the violet 450/50 channel when using UltraComp eBeads microspheres (Product # 01-2222-42) as compared to single-color stained cells. In such circumstances, we would recommend setting compensation with cells. We have also observed this in some experiments using AbC Total Antibody Compensation beads (Product # A10497).


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 μ L of cell sample + 100 μ L of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 405 nm; Emission: 780 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD117 (c-Kit) Monoclonal Antibody (2B8), Super Bright™ 780, eBioscience™



CD117 (c-Kit) Antibody (78-1171-82) in Flow

C57BL/6 mouse splenocytes were stained with Ly-6A/E (Sca-1) Monoclonal Antibody, PE (Product # 12-5981-82) and 0.06 μ g of Rat IgG2b kappa Isotype Control, Super Bright 780 (Product # 78-4031-82) (left) or 0.06 μ g of CD117 (c-kit) Monoclonal Antibody, Super Bright 780 (right). Cells in the Lineage negative/low gate were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

16 References

Western Blot (1)

Circulation research

Abi3bp regulates cardiac progenitor cell proliferation and differentiation.

"Published figure using CD117 (c-Kit) monoclonal antibody (Product # 78-1171-82) in Flow Cytometry"

Authors: Hodgkinson CP,Gomez JA,Payne AJ,Zhang L,Wang X,Dal-Pra S,Pratt RE,Dzau VJ

Year
2014

Immunocytochemistry (1)

Stem cells (Dayton, Ohio)

Bone marrow-derived myeloid progenitors in the leptomeninges of adult mice.

"Published figure using CD117 (c-Kit) monoclonal antibody (Product # 78-1171-82) in Immunocytochemistry"

Authors: Koeniger T,Bell L,Mifka A,Enders M,Hautmann V,Mekala SR,Kirchner P,Ekici AB,Schulz C,Wörsdörfer P, Mencl S,Kleinschnitz C,Ergün S,Kuerten S

Year
2021

Flow Cytometry (14)

Frontiers in pain research (Lausanne, Switzerland)

mMCP7, a Mouse Ortholog of Tryptase, Mediates Pelvic Tactile Allodynia in a Model of Chronic Pelvic Pain.

"Published figure using CD117 (c-Kit) monoclonal antibody (Product # 78-1171-82) in Flow Cytometry"

Authors: Pattabiraman G,Liu Z,Paul M,Schaeffer AJ,Thumbikat P

Year
2022

The Journal of biological chemistry

SNAP23 is essential for platelet and mast cell development and required in connective tissue mast cells for anaphylaxis.

"Published figure using CD117 (c-Kit) monoclonal antibody (Product # 78-1171-82) in Flow Cytometry"

Authors: Cardenas RA,Gonzalez R,Sanchez E,Ramos MA,Cardenas EI,Rodarte AI,Alcazar-Felix RJ,Isaza A,Burns AR, Heidelberg R,Adachi R

Year
2021

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.