

ICAM-1 Monoclonal Antibody (MEM-111), PE

Product Details	
Size	100 Tests
Species Reactivity	Bovine, Human, Rat
Published Species	Human
Host/Isotope	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	MEM-111
Conjugate	PE
Immunogen	Raji human Burkitt's lymphoma cell line
Form	Liquid
Purification	Size-exclusion chromatography
Storage buffer	PBS with 0.2% BSA
Contains	15mM sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11151852

Applications	Tested	Dilution	Published
Flow Cytometry (Flow)	✓	20 µL/1x10 ⁶ cells	2 Publications
Miscellaneous PubMed (MISC)	-		1 Publication

3 References

Flow Cytometry (2)

The American journal of pathology

Characterization and Purification of Neoplastic Cells of Nodular Lymphocyte Predominant Hodgkin Lymphoma from Lymph Nodes by Flow Cytometry and Flow Cytometric Cell Sorting.

"MA110249 was used in flow cytometry to document and describe lymphocyte predominant cells from lymph nodes involved in nodular lymphocyte predominant Hodgkin lymphoma"

Authors: Fromm JR,Thomas A,Wood BL

Species
Human

Dilution
Not Cited

Year
2017

American journal of clinical pathology

Identification and purification of classical Hodgkin cells from lymph nodes by flow cytometry and flow cytometric cell sorting.

"MA1-10249 was used in flow cytometry to evaluate the use of flow cytometry to identify the Hodgkin and Reed-Sternberg cells of classical Hodgkin lymphoma"

Authors: Fromm JR,Kussick SJ,Wood BL

Species
Not Applicable

Dilution
Not Cited

Year
2006

Miscellaneous PubMed (1)

International journal of hematology

Co-culture of hematopoietic stem cells with mesenchymal stem cells increases VCAM-1-dependent migration of primitive hematopoietic stem cells.

"MA1-10249 was used in flow cytometry to investigate how mesenchymal stem cells improve hematopoietic stem cell transplantability."

Authors: Perdomo-Arciniegas AM,Vernot JP

Species
Human

Dilution
Not Cited

Year
2011

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.