


# Vimentin Monoclonal Antibody (VI-01)

Product Details	
Size	100 µg
Species Reactivity	Mammal
Host/Isotope	Mouse / IgM
Class	Monoclonal
Type	Antibody
Clone	VI-01
Conjugate	Unconjugated
Immunogen	Pellet of pig brain cold stable proteins after depolymerization of Microtubules.
Form	Liquid
Concentration	1 mg/mL
Purification	Ammonium sulfate precipitation
Storage buffer	TBS, pH 8
Contains	15mM sodium azide
Storage Conditions	4° C, do not freeze
RRID	AB_1088258

Applications	Tested	Dilution	Published
Immunohistochemistry (Frozen) (IHC (F))	-	1:200	1 Publication
Immunocytochemistry (ICC)	✓	5 µg/mL	
Immunofluorescence (IF)	✓	5 µg/mL	
Western Blot (WB)	✓	1:2000	


**Vimentin Antibody (MA1-19168)**

Antibody specificity was demonstrated by detection of differential basal expression of the target across cell lines owing to their inherent genetic constitution. Relative expression of Vimentin was observed in all cell lines tested using product (Product # MA1-19168) in western blot. Relative expression validation info.



**Vimentin Antibody (MA1-19168)**


Antibody specificity was demonstrated by detection of differential basal expression of the target across cell models owing to their inherent genetic constitution. Immunofluorescence analysis using Vimentin Monoclonal Antibody (Product # MA1-19168) showed expression of Vimentin in HeLa compared to A431. Relative expression validation info.



## Product Images For Vimentin Monoclonal Antibody (VI-01)

### Vimentin Antibody (MA1-19168) in IF

Immunofluorescence analysis of Vimentin was performed using 70% confluent log phase HeLa cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with Vimentin Mouse Monoclonal Antibody (Product # MA1-19168) at 5 µg/ml in 0.1% BSA and incubated overnight at 4 degree Celsius and then labeled with Goat anti-Mouse IgG (H+L)/IgM (L) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A28175) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing cytoplasmic, cytoskeletal and nuclear localization. Panel e represents negative control, A-431 cells. Panel f represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.



[View more figures on thermofisher.com](#)

### 1 Reference

#### Immunohistochemistry (Frozen) (1)

##### Fertility and sterility

##### Bioengineered uterine tissue supports pregnancy in a rat model.

"MA1-19168 was used in immunohistochemistry - frozen section to study pregnancy in a rat model using bioengineered uterine tissue"

Authors: Hellström M, Moreno-Moya JM, Bandstein S, Bom E, Akouri RR, Miyazaki K, Maruyama T, Brännström M

##### Species

Not Applicable

##### Dilution

1:200

##### Year

2016

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.