

HMGB1 Monoclonal Antibody (HAP46.5)

Product Details	
Size	100 µL
Species Reactivity	Dog, Chicken, Human, Mouse, Rat
Published Species	Rat
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	HAP46.5
Conjugate	Unconjugated
Immunogen	Recombinant, full length, human HMGB1 protein.
Form	Liquid
Concentration	1.8 mg/mL
Purification	purified
Storage buffer	0.01M PBS
Contains	0.02% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2117462


Applications	Tested Dilution	Publications
Western Blot (WB)	0.5-1 µg/mL	1 Publication
ELISA (ELISA)	Assay-dependent	-

Product Specific Information


Recommended positive controls: MCF7.

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For HMGB1 Monoclonal Antibody (HAP46.5)



HMGB1 Antibody (MA1-20338)
Antibody specificity was demonstrated by showing that antibodies raised against the same target protein perform similarly. Western blot of HMGB1 using Anti-HMGB1 Monoclonal Antibody (Product # MA1-20338), tested in parallel with HMGB1 Monoclonal Antibody (Product # MA5-17278), shows similar expression of HMGB1 in the cell lines tested. {IAV}



HMGB1 Antibody (MA1-20338) in WB
Western blot analysis was performed on whole cell extracts (30 µg lysate) of RAW 264.7 (Lane 1), THP-1 (Lane 2), NIH/3T3 (Lane 3), MCF7 (Lane 4) and SH-SY5Y (Lane 5). The blot was probed with Anti-HMGB1 Monoclonal Antibody (Product # MA1-20338, 1 µg/ml) and detected by chemiluminescence using Goat anti-Mouse IgG (H+L) Superclonal™ Secondary Antibody, HRP conjugate (Product # A28177, 0.25 µg/ml, 1:4000 dilution). A 29 kDa band corresponding to HMGB1 was observed across the cell lines tested.

Western Blot (1)

Clinical science (London, England : 1979)	Year 2020
Greater high-mobility group box 1 in male compared with female spontaneously hypertensive rats worsens renal ischemia-reperfusion injury.	Species Rat
"MA1-20338 was used in Western Blotting to test the hypothesis that males have greater increases in the DAMP high-mobility group box 1 (HMGB1), worsening injury compared with females."	Dilution 1:1000
Authors: Mohamed R,Rafikova O,O'Connor PM,Sullivan JC	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.