

MUC2 Monoclonal Antibody (996/1)

Product Details	
Size	100 µg
Species Reactivity	Human
Published Species	Human
Host/Isotope	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	996/1
Conjugate	Unconjugated
Immunogen	MUC-2 tandem repeat peptide
Form	Liquid
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	PBS, pH 7.4
Contains	0.09% sodium azide
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_794978

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	Assay-Dependent	-
Immunohistochemistry (Frozen) (IHC (F))	Assay Dependent	-
Immunohistochemistry (Paraffin) (IHC (P))	Assay Dependent	-
Western Blot (WB)	Assay Dependent	-
Immunohistochemistry (IHC)	-	5 Publications

Product Specific Information

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

5 References

Immunohistochemistry (5)

Gut and liver

Microsatellite Instability of Gastric and Colorectal Cancers as a Predictor of Synchronous Gastric or Colorectal Neoplasms.

"MA1-25020 was used in immunohistochemistry to utilize a predictor for synchronous colorectal or gastric neoplasms by presence of microsatellite instability of colorectal and gastric cancers"

Authors: Kim YB, Lee SY, Kim JH, Sung IK, Park HS, Shim CS, Han HS

Species
Not Applicable

Dilution
1:2000

Year
2016

Clinical endoscopy

Early Gastric Cancer-Like Advanced Gastric Cancer versus Advanced Gastric Cancer-Like Early Gastric Cancer.

"MA1-25020 was used in immunohistochemistry to study endoscopic differences between early gastric cancer that resembles advanced gastric cancer and advanced gastric cancer that resembles early gastric cancer"

Authors: Park HS, Lee SY, Hong SN, Kim JH, Sung IK, Park HS, Shim CS, Jin CJ

Species
Human

Dilution
1:2000

Year
2013

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.