

CD254 (RANK Ligand) Monoclonal Antibody (12A380)


Product Details	
Size	100 µg
Species Reactivity	Human, Mouse
Host/Isotype	Mouse / IgG1, kappa
Class	Monoclonal
Type	Antibody
Clone	12A380
Conjugate	Unconjugated
Immunogen	Bacterially expressed fusion protein containing residues 1-317 of mouse RANK ligand.
Form	Liquid
Concentration	1.0 mg/mL
Purification	Protein G
Storage buffer	PBS
Contains	0.05% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_1087030

Applications	Tested Dilution	Publications
Western Blot (WB)	4-6 µg/mL	-
Immunohistochemistry (Paraffin) (IHC (P))	1:50-1:250	-
Immunohistochemistry (Frozen) (IHC (F))	1:10-1:500	-
Immunocytochemistry (ICC/IF)	Assay-Dependent	-
Flow Cytometry (Flow)	1:10-1:1,000	1 Publication

Product Specific Information


Suggested positive control: activated T cells or RAW cells, antigen standard for TNFSF11 (transient overexpression lysate).

Product Images For CD254 (RANK Ligand) Monoclonal Antibody (12A380)




CD254 (RANK Ligand) Antibody (MA1-41019) in IHC (P)

Immunohistochemical analysis of CD254 (RANK Ligand) in formalin-fixed paraffin-embedded human tonsil. Samples were incubated in CD254 (RANK Ligand) monoclonal antibody (Product # MA1-41019) using a dilution of 0.0763888888888889. Bond Rx autostainer (Leica Biosystems). The assay involved 20 minutes of heat induced antigen retrieval (HIER) using 10mM sodium citrate buffer (pH 6.0) and endogenous peroxidase quenching with peroxide block. The sections were incubated with primary antibody for 30 minutes and Bond Polymer Refine Detection (Leica Biosystems) with DAB was used for signal development followed by counterstaining with hematoxylin. Whole slide scanning and capturing of representative images was performed using Aperio AT2 (Leica Biosystems). Cytoplasmic staining was observed. Staining was performed by Histowiz.



CD254 (RANK Ligand) Antibody (MA1-41019) in Flow

Flow cytometry of of CD254 (RANK Ligand) in RAW cells. Frozen samples were incubated in CD254 (RANK Ligand) monoclonal antibody (Product # MA1-41019) using a dilution of 2 µg/mL. Shaded histogram represents cells without antibody; green represents isotype control antibody; purple represents antibody. Image using the PE format of this antibody.



CD254 (RANK Ligand) Antibody (MA1-41019) in Flow

Flow cytometry of CD254 (RANK Ligand) in RANKL in untreated mouse splenocytes (green) and 72 hour ConA-stimulated mouse splenocytes (red). Samples were incubated in CD254 (RANK Ligand) monoclonal antibody (Product # MA1-41019) using a dilution of 1.0 µg. Antibody was conjugated to Alexa Fluor (R) 488.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Flow Cytometry (1)

International journal of molecular medicine

BuShenNingXin decoction suppresses osteoclastogenesis by modulating RANKL/OPG imbalance in the CD4+ T lymphocytes of ovariectomized mice.

Year
2018

"Published figure using CD254 (RANK Ligand) monoclonal antibody (Product # MA1-41019) in Flow Cytometry"

Authors: Zhang JL,Qiu XM,Zhang N,Tang W,Gober HJ,Li DJ,Wang L

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.