

HSP70 Monoclonal Antibody (3A3)

Product Details

Size	50 µg
Species Reactivity	Amphibian, Arthropod, Avian, Dog, Fruit fly, Fish, Human, Mollusc, Mouse, Non-human primate, Plant, Pig, Rat, Yeast
Published Species	Algae, Rat, Yeast, Pig, Insect, Non-human primate, Mollusc, Amphibian, Crab, Arthropod, Fish, Human, Mouse, Echinoderm, Prawn, Fruit fly
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	3A3
Conjugate	Unconjugated
Immunogen	Human recombinant HSP70 overexpressed in E. coli.
Form	Liquid
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	PBS
Contains	0.05% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_325454

Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000-1:5,000	64 Publications
Immunohistochemistry (IHC)	-	3 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:200	-
Immunocytochemistry (ICC/IF)	1:100	4 Publications
Flow Cytometry (Flow)	-	1 Publication
ELISA (ELISA)	-	3 Publications
Immunoprecipitation (IP)	2 µL	2 Publications
Neutralization (Neu)	-	1 Publication
Gel Shift (GS)	Assay-dependent	-
Miscellaneous PubMed (Misc)	-	2 Publications

Product Specific Information

MA3-006 detects several members of the heat shock protein 70 kDa (HSP70) gene family including HSP70, HSC70, p75, and following heat shock, HSP72 from yeast, Drosophila, fish, porcine, plant, mouse, avian, arthropod (red claw crayfish & black tiger prawn), amphibian, non-human primate, and human samples.

MA3-006 has been successfully used in Western blot, immunocytochemistry, immunofluorescence, gel shift, and immunoprecipitation procedures. By Western blot, this antibody detects proteins from ~70 kDa to ~78 kDa representing different members of the HSP70 family. 2-dimensional gel electrophoresis is required to resolve the heat induced form of these proteins from their constitutively expressed counterparts. Immunocytochemical staining of HSP70 in heat shocked HeLa cells


with MA3-006 results in cytoplasmic staining.

The MA3-006 antigen is recombinant human HSP70 over-expressed in E. coli. Epitope mapping with a panel of HSP70 deletion mutants suggests that the epitope recognized is located between amino acids 504-617 of human HSP70, a region that has been shown to be involved in stress-induced nucleolar localization.

Product Images For HSP70 Monoclonal Antibody (3A3)


HSP70 Antibody (MA3-006)

Altered expression of proteins upon cell treatment demonstrates antibody specificity. Western blot using HSP70 Monoclonal Antibody (3A3) (Product # MA3-006), shows increased expression of proteins upon heat shock treatment. {TM}




HSP70 Antibody (MA3-006) in ICC/IF

Immunofluorescent analysis of Heat Shock Protein 70 (Hsp70) (green) in HeLa and NIH3T3 cells. Formalin fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 10 minutes at room temperature and blocked with 1% Blocker BSA (Product # 37525) for 15 minutes at room temperature. Cells were probed with a Hsp70 monoclonal antibody (Product # MA3-006), at a dilution of 1:50 for at least 1 hour at room temperature, washed with PBS, and incubated with DyLight 488 goat-anti-mouse IgG secondary antibody (Product # 35502) at a dilution of 1:400 for 30 minutes at room temperature. Nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Images were taken on a Thermo Scientific ArrayScan at 20X magnification.



HSP70 Antibody (MA3-006) in ICC/IF

Immunofluorescent analysis of Heat Shock Protein 70 using Heat Shock Protein 70 Monoclonal antibody (3A3) (Product # MA3-006) shows staining in HeLa cells. Heat Shock Protein 70 staining (green), F-Actin staining with Phalloidin (red) and nuclei with DAPI (blue) is shown. Cells were grown on chamber slides and fixed with formaldehyde prior to staining. Cells were probed without (control) or with or an antibody recognizing Heat Shock Protein 70 (Product # MA3-006) at a dilution of 1:100-1:200 over night at 4 °C, washed with PBS and incubated with a DyLight-488 conjugated secondary antibody (Product # 35552 for GAR, Product # 35503 for GAM). Images were taken at 60X magnification.



View more figures on thermofisher.com

Western Blot (64)

Biomedicines	
gp130 Activates Mitochondrial Dynamics for Hepatocyte Survival in a Model of Steatohepatitis.	Year 2023
"MA3-006 was used in Western Blotting to investigate the effect of gp130 on the components of mitochondrial dynamics in a cellular model of steatohepatitis."	Species Human
Authors: Shunkina D,Dakhnevich A,Shunkin E,Khaziakhmatova O,Shupletsova V,Vulf M,Komar A,Kirienkova E, Litvinova L	
Nature communications	
Nanoscale segregation of channel and barrier claudins enables paracellular ion flux.	Year 2022
"MA3-006 was used in Sample Preparation to suggest that nanoscale segregation of distinct channel-forming claudins enables barrier function combined with specific paracellular ion flux across tight junctions."	Species Mouse
Authors: Gonschior H,Schmied C, Van der Veen RE,Eichhorst J,Himmerkus N,Piontek J,Günzel D,Bleich M,Furuse M, Haucke V,Lehmann M	Dilution 1:5000

View more WB references on thermofisher.com

Immunohistochemistry (3)

Journal of immunology research	
Neuroprotective Effects of <i>Asparagus officinalis</i> Stem Extract in Transgenic Mice Overexpressing Amyloid Precursor Protein.	Year 2021
"Published figure using HSP70 monoclonal antibody (Product # MA3-006) in Immunohistochemistry"	
Authors: Peng Z,Bedi S,Mann V,Sundaresan A,Homma K,Gaskey G,Kowada M,Umar S,Kulkarni AD,Eltzschig HK, Doursout MF	
Fish & shellfish immunology	
Histological, ultrastructural and heat shock protein 70 (HSP70) responses to heat stress in the sea cucumber <i>Apostichopus japonicus</i>.	Year 2015
"MA3-006 was used in immunohistochemistry and western blot to study HSP70 in <i>Apostichopus japonicus</i> "	Species Echinoderm
Authors: Xu D,Sun L,Liu S,Zhang L,Yang H	Dilution 1:200

View more IHC references on thermofisher.com

More applications with references on thermofisher.com

- ICC/IF (4)
- Flow (1)
- ELISA (3)
- IP (2)
- Neu (1)
- Misc (2)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.