

Tau Monoclonal Antibody (TAU-5)

Product Details	
Size	500 µL
Species	Bovine, Human, Mouse, Sheep, Rat
Published Species	Rat, Human, Mouse
Expression System	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	TAU-5
Conjugate	Unconjugated
Immunogen	Purified bovine microtubule-associated proteins
Form	Liquid
Concentration	0.2 mg/mL
Purification	Protein G
Storage buffer	PBS, pH 7.4, with 0.2% BSA
Contains	0.09% sodium azide
Storage Conditions	4° C
RRID	AB_10980631

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC)	2-3 µg/mL	3 Publications
Immunofluorescence (IF)	2-3 µg/mL	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	1:100	1 Publication
Immunoprecipitation (IP)	2 µg/mg protein lysate	3 Publications
Western Blot (WB)	1-2 µg/mL	55 Publications
ELISA (ELISA)	-	1 Publication
Immunohistochemistry (IHC)	-	1 Publication
Miscellaneous PubMed (Misc)	-	4 Publications

Product Specific Information


MA5-12808 targets TAU in immunofluorescence, immunoprecipitation, and Western blot applications and shows reactivity with Bovine, Human, mouse, Ovine, and Rat samples.

The MA5-12808 immunogen is purified bovine microtubule-associated proteins.

Product Images For Tau Monoclonal Antibody (TAU-5)


Tau Antibody (MA5-12808) in IF

Immunofluorescence analysis of TAU was done on 70% confluent log phase SH-SY5Y cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with TAU (TAU-5) Mouse Monoclonal Antibody (Product # MA5-12808) at 2 µg/mL in 0.1% BSA and incubated for 3 hours at room temperature and then labeled with Goat anti-Mouse IgG (H+L) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A28175) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Alexa Fluor® 555 Rhodamine Phalloidin (Product # R415, 1:300). Panel d is a merged image showing cytoplasmic localization. Panel e is a no primary antibody control. The images were captured at 60X magnification.




Tau Antibody (MA5-12808) in IHC (P)

Immunohistochemistry analysis of TAU (TAU-5) showing staining in the cytoplasm of paraffin-embedded mouse brain tissue (right) compared to a negative control without primary antibody (left). To expose target proteins, antigen retrieval was performed using 10mM sodium citrate (pH 6.0), microwaved for 8-15 min. Following antigen retrieval, tissues were blocked in 3% H₂O₂-methanol for 15 min at room temperature, washed with ddH₂O and PBS, and then probed with a TAU Antibody (TAU-5) Mouse Monoclonal Antibody (Product # MA5-12808) diluted in 3% BSA-PBS at a dilution of 1:100 for 1 hour at 37°C in a humidified chamber. Tissues were washed extensively in PBST and detection was performed using an HRP-conjugated secondary antibody followed by colorimetric detection using a DAB kit. Tissues were counterstained with hematoxylin and dehydrated with ethanol and xylene to prep for mounting.



Tau Antibody (MA5-12808) in IHC (P)

Immunohistochemistry analysis of TAU (TAU-5) showing staining in the cytoplasm of paraffin-embedded human astrogloma (right) compared to a negative control without primary antibody (left). To expose target proteins, antigen retrieval was performed using 10mM sodium citrate (pH 6.0), microwaved for 8-15 min. Following antigen retrieval, tissues were blocked in 3% H₂O₂-methanol for 15 min at room temperature, washed with ddH₂O and PBS, and then probed with a TAU Antibody (TAU-5) Mouse Monoclonal Antibody (Product # MA5-12808) diluted in 3% BSA-PBS at a dilution of 1:100 for 1 hour at 37°C in a humidified chamber. Tissues were washed extensively in PBST and detection was performed using an HRP-conjugated secondary antibody followed by colorimetric detection using a DAB kit. Tissues were counterstained with hematoxylin and dehydrated with ethanol and xylene to prep for mounting.



[View more figures on thermofisher.com](https://www.thermofisher.com)

Immunofluorescence (1)

Frontiers in neuroscience

Oxidative Stress Modifies the Levels and Phosphorylation State of Tau Protein in Human Fibroblasts.

"Published figure using Tau monoclonal antibody (Product # MA5-12808) in Immunofluorescence"

Authors: Ibáñez-Salazar A, Bañuelos-Hernández B, Rodríguez-Leyva I, Chi-Ahumada E, Monreal-Escalante E, Jiménez-Capdeville ME, Rosales-Mendoza S

Species
Not Applicable

Dilution
Not Cited

Year
2020

Western Blot (55)

Frontiers in neuroscience

Oxidative Stress Modifies the Levels and Phosphorylation State of Tau Protein in Human Fibroblasts.

"Published figure using Tau monoclonal antibody (Product # MA5-12808) in Immunofluorescence"

Authors: Ibáñez-Salazar A, Bañuelos-Hernández B, Rodríguez-Leyva I, Chi-Ahumada E, Monreal-Escalante E, Jiménez-Capdeville ME, Rosales-Mendoza S

Species
Not Applicable

Dilution
Not Cited

Year
2020

Frontiers in molecular neuroscience

Effects of APOE Genotype on Brain Proteomic Network and Cell Type Changes in Alzheimer's Disease.

"MA5-12808 was used in Western Blotting to reveal alterations in the brain proteome and brain cell types associated with allelic variants in APOE, and suggest further areas for investigation into the upstream mechanisms that drive ApoE-associated risk for AD."

Authors: Dai J, Johnson ECB, Dammer EB, Duong DM, Gearing M, Lah JJ, Levey AI, Wingo TS, Seyfried NT

Species
Human

Dilution
1:1000

Year
2020

[View more WB references on thermofisher.com](#)

Immunoprecipitation (3)

Proteomics

Quantitative Analysis of the Brain Ubiquitylome in Alzheimer's Disease.

"MA5-12808 was used in Immunoprecipitation to map changes in the Alzheimer's Disease (AD) brain ubiquitylome using an immunoaffinity enrichment approach coupled to mass spectrometry analysis."

Authors: Abreha MH, Dammer EB, Ping L, Zhang T, Duong DM, Gearing M, Lah JJ, Levey AI, Seyfried NT

Species
Human

Dilution
Not Cited

Year
2018

[View more IP references on thermofisher.com](#)

More applications with references on thermofisher.com

Misc (4) IHC (1) ICC (3) ELISA (1) IHC (P) (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.