

# Phospho-AKT1 (Ser473) Monoclonal Antibody (14-6)

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse
Published Species	Rat, Mouse, Human
Host/Isotype	Rabbit / IgG
Class	Monoclonal
Type	Antibody
Clone	14-6
Conjugate	Unconjugated
Immunogen	Synthetic phosphopeptide derived from a region of human PKB that contains serine 473.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A
Storage buffer	Dulbecco's PBS, pH 7.3, with 1mg/mL BSA, 50% glycerol
Contains	0.05% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_557533

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500	8 Publications
Immunocytochemistry (ICC/IF)	1:100	-

## Product Specific Information


OMA1-03061 detects protein kinase B (PKB) phosphorylated at Ser473 from human and mouse samples. OMA1-03061 detects PKB 1,2,and 3.

OMA1-03061 has been successfully used in Western blot, immunofluorescence, and immunocytochemistry procedures. By Western blot, this antibody detects an ~55 kDa protein representing phosphorylated PKB (Ser473) from NIH-3T3 cells treated with platelet-derived growth factor (PDGF).

The OMA1-03061 immunizing phosphopeptide was derived from a region of human PKB that contains serine 473. There is 100% homology with other species, that have not yet been tested.

Antibodies to this protein (and modification) were previously sold as part of a Thermo Scientific Cellomics High Content Screening Kit. This replacement antibody is now recommended for researchers who need an antibody for high content cell based assays. It has been thoroughly tested and validated for cellular immunofluorescence (IF) applications. Further optimization including the selection of the most appropriate fluorescent Dylight conjugated secondary antibody may have to be performed for your high content assay.

Product Images For Phospho-AKT1 (Ser473) Monoclonal Antibody (14-6)




Phospho-AKT1 (Ser473) Antibody (OMA1-03061) in WB

Western blot analysis was performed on whole cell extracts (30 µg lysate) of A-431 (Lane 1), A-431 treated with EGF (200 ng/mL for 10 min) (Lane 2), A-431 treated with MK-2206 (5 uM for 5 h) followed by EGF treatment (200 ng/mL for 10 min) (Lane 3), NIH/3T3 (Lane 4), NIH/3T3 treated with PDGF (20 ng/mL for 30 min) (Lane 5), NIH/3T3 treated with MK-2206 (5uM for 5 h) followed by PDGF (20 ng/mL for 30 min) (Lane 6), PC-3 (Lane 7), PC-3 treated with Wortmannin (2 uM for 1 h) (Lane 8) and U-87 MG (Lane 9). The blot was probed with Anti-Phospho-AKT1 (Ser473) Monoclonal Antibody (Product # OMA1-03061, 1:500 dilution) and detected by chemiluminescence using Goat anti-Rabbit IgG (Heavy Chain) Superclonal™ Secondary Antibody, HRP conjugate (Product # A27036, 0.25 µg/mL, 1:4000 dilution). A 56 kDa band corresponding to Phospho-AKT1 (Ser473) was enhanced upon growth factor treatment across the cell lines tested and reduced upon drug treatment.


Phospho-AKT1 (Ser473) Antibody (OMA1-03061)

Altered expression of proteins upon cell treatment demonstrates antibody specificity. Western blot using Phospho-AKT1 (Ser473) Monoclonal Antibody (Product # OMA1-03061) shows increased expression of protein phosphorylated at the serine residues in A-431 treated with EGF and NIH/3T3 treated with PDGF. Pre-treatment with AKT-antagonist MK-2206 resulted in inhibition of Phospho-AKT1 (Ser473) in A-431 and NIH/3T3. Treatment of PC-3 with PI3K-antagonist, Wortmannin, also showed reduction in Phospho-AKT1 (Ser473). {TM}



Phospho-AKT1 (Ser473) Antibody (OMA1-03061) in WB

Western blot analysis of LanthaScreen™ and CellSensor® cell lines using a phospho-AKT pSer473 monoclonal antibody (Product # OMA1-03061). (A) LanthaScreen™ GFP-AKT HEK293E cells were treated under the indicated conditions, including IGF-1 (Product # PHG9071), LY294002 (Product # PHZ1144), and wortmannin (Product # PHZ1301). Cell extracts were resolved by SDS-PAGE and transferred to nitrocellulose with the iBlot® Gel Transfer Device (Product # IB1001). The membrane was then probed with the anti-AKT (PS473) PSSA (Product # OMA1-03061), and the signal was detected using a WesternBreeze® Chromogenic Kit (Product # WB7105). (B) CellSensor® T REx™ FOXO3 DBE-bla HeLa cell lysates were generated by treatment with doxycycline to induce FOXO3 expression, followed by incubation with the indicated stimulants or inhibitors and lysis. The nitrocellulose membrane was prepared and developed as in (A), except that the PSSA used in this case was anti-FOXO3 (PT32) (Product # 44-1240G).



View more figures on [thermofisher.com](https://thermofisher.com)

Western Blot (8)

Renal failure	Year 2021
<b>Implications of cell division cycle associated 4 on the Wilm's tumor cells viability via AKT/mTOR signaling pathway.</b>	
"Published figure using Phospho-AKT1 (Ser473) monoclonal antibody (Product # OMA1-03061) in Western Blot"	
Authors: Li S,Qin C,Chen Y,Wei D,Tan Z,Meng J	
Cell & bioscience	Year 2020
<b>New insights on thyroid hormone mediated regulation of herpesvirus infections.</b>	Species Human
"OMA103061 was used in western blot to discuss the roles of T3 in the regulation of HSV-1 replication during latency and reactivation"	Dilution 1:1000
Authors: Figliozzi RW,Chen F,Hsia SV	

[View more WB references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.