

Ezrin Monoclonal Antibody (3C12)

Product Details

Size	500 µL
Published Species	Dog, Rat, Human, Mouse
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	3C12
Conjugate	Unconjugated
Immunogen	A recombinant fragment of human ezrin corresponding to aa 362-585
Form	Liquid
Concentration	0.2 mg/mL
Storage conditions	4° C
RRID	AB_10979020


Applications	Tested Dilution	Publications
Western Blot (WB)	0.5-1.0 µg/mL	15 Publications
Immunohistochemistry (IHC)	-	24 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1-2 µg/mL	7 Publications
Immunocytochemistry (ICC/IF)	1:50-1:200	8 Publications
Immunoprecipitation (IP)	2 µg/mL	1 Publication
in situ PLA (PLA)	-	1 Publication
Miscellaneous PubMed (Misc)	-	5 Publications

Product Specific Information

MA5-13862 targets Ezrin in IHC (P), ICC, IP, IF, and WB applications and shows reactivity with Bovine, Hamster, Human, Marsupial, mouse, Non-human primate, and Rat samples.

The MA5-13862 immunogen is a recombinant fragment of human ezrin corresponding to aa 362-585.

Product Images For Ezrin Monoclonal Antibody (3C12)




Ezrin Antibody (MA5-13862)

Antibody specificity was demonstrated by CRISPR-Cas9 mediated knockout of target protein. A loss of signal was observed for target protein in HeLa Cas9 cell line transduced with Ezrin Lentiviral sgRNA compared to control cell line using Anti-Ezrin Monoclonal Antibody (3C12) (Product # MA5-13862). {KO}


Ezrin Antibody (MA5-13862)

The specificity of anti-Ezrin monoclonal antibody (Product # MA5-13862) was demonstrated by siRNA knockdown. Western blot analysis of HeLa cell extracts using this antibody showed decreased level of Ezrin protein expression in cells transfected with Ezrin (VIL-2) specific siRNA (lane 3) but not in controls (lane 1 and 2). {KD}



Ezrin Antibody (MA5-13862) in ICC/IF

Immunofluorescent analysis of Phalloidin (magenta) and Ezrin (green) in A431 cells. Formalin fixed cells were permeabilized with 0.1% Triton X-100 in PBS for 10 minutes at room temperature and blocked with 2% BSA (Product # 37525) in PBS + 0.1% Triton X-100 for 30 minutes at room temperature. Cells were probed with an Ezrin monoclonal antibody (Product # MA5-13862) at a dilution of 1:75 for at least 1 hour at room temperature, washed with PBS, and incubated with DyLight 488 goat anti-mouse IgG secondary antibody (Product # 35502) at a dilution of 1:250 for 30 minutes at room temperature. Actin was stained with DyLight 633 Phalloidin (Product # 21840) at a dilution of 1:120 (2.5units/mL final concentration) and nuclei (blue) were stained with Hoechst (Product # 62249) at a concentration of 1 µg/mL for 30 minutes. Images were taken on a Zeiss Axio Observer Z1 microscope at 20X magnification.



View more figures on thermofisher.com

Western Blot (15)

Cells

Mechanism of Dyslipidemia in Obesity-Unique Regulation of Ileal Villus Cell Brush Border Membrane Sodium-Bile Acid Cotransport.

"MA5-13862 was used in Western Blotting to demonstrate that in an epidemic condition, obesity, the dyslipidemia that leads to many of the complications of the condition, may, at least in part, be due to deregulation of intestinal bile acid absorption."

Authors: Sundaram S,Palaniappan B,Nepal N,Chaffins S,Sundaram U,Arthur S

Year
2019

Species
Rat

Oncotarget

CPI-17 drives oncogenic Ras signaling in human melanomas via Ezrin-Radixin-Moesin family proteins.

"MA513862 was used in western blot to explore how C-kinase potentiated protein phosphatase-1 inhibitor of 17 kDa drives Ras activity and tumorigenesis"

Authors: Riecken LB,Zoch A,Wiehl U,Reichert S,Scholl I,Cui Y,Ziemer M,Anderegg U,Hagel C,Morrison H

Year
2016

Species
Human

[View more WB references on thermofisher.com](#)

Immunohistochemistry (24)

Cells

Role of FGF and Hyaluronan in Choroidal Neovascularization in Sorsby Fundus Dystrophy.

"MA5-13862 was used in Immunohistochemistry to gain further insight into the molecular mechanism(s) by which mutant tissue inhibitor of metalloproteinase-3 (TIMP3) induces choroidal neovascularization (CNV)."

Authors: Wolk A,Hatipoglu D,Cutler A,Ali M,Bell L,Hua Qi J,Singh R,Batoki J,Karle L,Bonilha VL,Wessely O,Stoehr H, Hascall V,Anand-Apte B

Year
2020

Species
Mouse

Pflugers Archiv : European journal of physiology

The adenosine A2B receptor is involved in anion secretion in human pancreatic duct Capan-1 epithelial cells.

"MA513862 was used in immunohistochemistry to find that adenosine A2B receptors on the luminal membranes of Capan-1 cells are the functional adenosine receptors and Cl(-) channels important for anion secretion"

Authors: Hayashi M,Inagaki A,Novak I,Matsuda H

Year
2016

Species
Rat

Dilution
1:400

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

IHC (P) (7)

ICC/IF (8)

IP (1)

PLA (1)

Misc (5)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.