

Adiponectin Polyclonal Antibody

Product Details	
Size	200 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotope	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptides corresponding to the residues E(18) D D V T T T E E L A P A L V(32) and F(187) T Y D Q Y Q E K N V D Q A(200) of mouse Adiponectin.
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	PBS with 1mg/mL BSA
Contains	0.05% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_325789


Applications	Tested	Dilution	Published
Western Blot (WB)	✓	2 µg/mL	17 Publications
Blocking Assay (BLOCK)	-		1 Publication
Immunohistochemistry (IHC)	-		2 Publications
Immunocytochemistry (ICC)	✓	2 µg/mL	1 Publication
Immunofluorescence (IF)	✓	2 µg/mL	
Immunoprecipitation (IP)	✓	Assay dependent	

Product Specific Information

PA1-054 detects Adiponectin (30 kDa) from mouse serum.


PA1-054 has been successfully used in Western blot and immunoprecipitation procedures. By Western blot, this antibody detects an ~30 kDa protein representing Adiponectin from mouse serum.

The PA1-054 immunogen is a pair of synthetic peptides corresponding to the residues E(18) D D V T T T E E L A P A L V(32) and F(187) T Y D Q Y Q E K N V D Q A(200) of mouse Adiponectin.



Adiponectin Antibody (PA1-054)

Antibody specificity was demonstrated by showing that antibodies raised against the same target protein perform similarly. Western blot of Adiponectin using Anti-Adiponectin Polyclonal Antibody (Product # PA1-054), tested in parallel with Adiponectin ABfinity™ Oligoclonal Antibody (Product # 710179), shows similar expression of Adiponectin in the samples tested. Independent antibody validation info.




Adiponectin Antibody (PA1-054)

Modulation of expression of target protein by cell treatment to demonstrate antibody specificity. Immunofluorescence analysis of Adiponectin using anti-Adiponectin Polyclonal antibody (Product # PA1-054) shows increased expression of Leptin in differentiated 3T3-L1 cells. Cell Treatment validation info.

Product Images For Adiponectin Polyclonal Antibody

Fig. 1



Adiponectin Antibody (PA1-054) in WB

Western blot detection of Adiponectin from mouse serum using Product # PA1-054.

View more figures on thermofisher.com

21 References

Western Blot (17)

PloS one

Aortic carboxypeptidase-like protein enhances adipose tissue stromal progenitor differentiation into myofibroblasts and is upregulated in fibrotic white adipose tissue.

Authors: Jager M, Lee MJ, Li C, Farmer SR, Fried SK, Layne MD

Species
Mouse

Dilution
Not Cited

Year
2018

Journal of extracellular vesicles

Characterisation of adipocyte-derived extracellular vesicle subtypes identifies distinct protein and lipid signatures for large and small extracellular vesicles.

"PA1054 was used in western blot to describe extracellular vesicle subpopulations secreted by fat cells"

Authors: Durcin M, Fleury A, Taillebois E, Hilairret G, Krupova Z, Henry C, Truchet S, Trötmüller M, Köfeler H, Mabileau G, Hue O, Andriantsitohaina R, Martin P, Le Lay S

Species
Mouse

Dilution
Not Cited

Year
2018

[View more WB references on thermofisher.com](#)

Blocking Assay (1)

The Journal of endocrinology

Adipocytes play an etiological role in the podocytopathy of high-fat diet-fed rats.

"PA1054 was used in blocking or activating experiment to elucidate the relationship between obesity and chronic kidney disease"

Authors: Chen JY, Jian DY, Lien CC, Lin YT, Ting CH, Chen LK, Hsu TC, Huang HM, Wu YT, Kuan TT, Chao YW, Wu LY, Huang SW, Juan CC

Species
Mouse

Dilution
Not Cited

Year
2016

Immunohistochemistry (2)

The Journal of biological chemistry

T-cadherin is essential for adiponectin-mediated revascularization.

"PA1-054 was used in immunohistochemistry to study the role of T-cadherin in the mechanism by which adiponectin promotes revascularization"

Authors: Parker-Duffen JL, Nakamura K, Silver M, Kikuchi R, Tigges U, Yoshida S, Denzel MS, Ranscht B, Walsh K

Species
Mouse

Dilution
Not Cited

Year
2013

More applications with references on thermofisher.com

ICC (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.