

# Bax Monoclonal Antibody (2D2)

Product Details	
Size	500 µL
Species Reactivity	Human
Published Species	Rat, Human
Host/Isotope	Mouse / IgG1, kappa
Class	Monoclonal
Type	Antibody
Clone	2D2
Conjugate	Unconjugated
Immunogen	A synthetic peptide, aa 3-16 (Cys-GSGEQPRGGGPTSS) of human bax protein. This amino acid sequence is NOT shared by mouse and rat bax protein.
Form	Liquid
Concentration	0.2 mg/mL
Purification	Protein G
Storage buffer	PBS, pH 7.4, with 0.2% BSA
Contains	0.09% sodium azide
Storage Conditions	4° C
RRID	AB_11004781


Applications	Tested	Dilution	Published
Immunocytochemistry (ICC)	-		2 Publications
Immunohistochemistry (IHC)	-	1:100	26 Publications
Western Blot (WB)	✓	1 µg/mL	15 Publications
Immunohistochemistry (Paraffin) (IHC (P))	✓	2-4 µg/mL	2 Publications
Miscellaneous PubMed (MISC)	-	1:40	4 Publications
Immunofluorescence (IF)	✓	Assay Dependent	

## Product Specific Information

MA5-13994 targets Bax in IF, IHC (P), and WB applications and shows reactivity with Human samples.


The MA5-13994 immunogen is a synthetic peptide, aa 3-16 (Cys-GSGEQPRGGGPTSS) of human bax protein. This amino acid sequence is NOT shared by mouse and rat bax protein.

## Product Images For Bax Monoclonal Antibody (2D2)



### Bax Antibody (MA5-13994) in IHC

Formalin-fixed, paraffin-embedded human Hodgkin's lymphoma stained with Bax antibody using peroxidase-conjugate and DAB chromogen. Note membrane staining of Reed-Sternberg cells.



### Bax Antibody (MA5-13994) in WB

Western blot of Bax using Bax Monoclonal Antibody (Product # MA5-13994) on HeLa Cells.

## 49 References

### Immunocytochemistry (2)

#### Cell death and differentiation

#### Cardiolipin or MTCH2 can serve as tBID receptors during apoptosis.

"MA5-13994 was used in immunocytochemistry to research tBID receptors served by MTCH2 or Cardiolipin during apoptosis"

Authors: Raemy E, Montessuit S, Pierredon S, van Kampen AH, Vaz FM, Martinou JC

#### Species

Not Applicable

#### Dilution

Not Cited

#### Year

2016

#### Ophthalmic research

#### Modulation of Ku70/80, clusterin/ApoJ isoforms and Bax expression in indocyanine-green-mediated photo-oxidative cell damage.

"MA5-13994 was used in immunocytochemistry to study the molecular mechanisms underlying indocyanine-green-mediated photo-oxidative cell damage"

Authors: Ricci F, Pucci S, Sesti F, Missiroli F, Cerulli L, Spagnoli LG

#### Species

Human

#### Dilution

Not Cited

#### Year

2007

### Immunohistochemistry (26)

#### Toxicology and industrial health

#### The protective effects of carnosine in alcohol-induced hepatic injury in rats.

"MA5-13994 was used in immunohistochemistry to study the mechanisms underlying the protective effects of carnosine in a rat model of alcohol-induced liver damage"

Authors: Baykara B, Micili SC, Tugyan K, Tekmen I, Bagriyanik H, Sonmez U, Sonmez A, Oktay G, Yener N, Ozbal S

#### Species

Rat

#### Dilution

1:100

#### Year

2014

#### Cancer

#### Combination of molecular alterations and smoking intensity predicts bladder cancer outcome: a report from the Los Angeles Cancer Surveillance Program.

"MA5-13994 was used in immunohistochemistry to study the value of a panel of 9 biomarkers plus smoking intensity in predicting the outcome of bladder cancer"

Authors: Mitra AP, Castelao JE, Hawes D, Tsao-Wei DD, Jiang X, Shi SR, Datar RH, Skinner EC, Stein JP, Groshen S, Yu MC, Ross RK, Skinner DG, Cortesiss VK, Cote RJ

#### Species

Human

#### Dilution

1:400

#### Year

2013

[View more IHC references on thermofisher.com](#)

### More applications with references on thermofisher.com

WB (15)

IHC (P) (2)

MISC (4)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.