

Phospho-Aurora A (Thr288) Monoclonal Antibody (F.131.2)

Product Details	
Size	100 µL
Species Reactivity	Human
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Monoclonal
Type	Antibody
Clone	F.131.2
Conjugate	Unconjugated
Immunogen	Synthetic phosphopeptide corresponding to residues around pThr288 of human Aurora A
Form	Liquid
Concentration	334 µg/mL
Purification	Affinity chromatography
Storage buffer	0.01M HEPES, pH 7.5, with 0.15M NaCl, 100µg/mL BSA, 50% glycerol
Contains	<0.02% sodium azide
Storage conditions	-20°C
RRID	AB_10983549


Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	2 Publications
Immunocytochemistry (ICC/IF)	1:1,600	1 Publication

Product Specific Information


It is not recommended to aliquot this antibody.

Product Images For Phospho-Aurora A (Thr288) Monoclonal Antibody (F.131.2)


Phospho-Aurora A (Thr288) Antibody (MA5-14904) in WB
Western blot analysis of Phospho-Aurora A pThr288 in extracts from HeLa and HT29 cells, hydroxyurea or nocodazole-treated, using Phospho-Aurora A pThr288 monoclonal antibody (Product # MA5-14904).



Phospho-Aurora A (Thr288) Antibody (MA5-14904)
Altered expression of target protein between dividing and resting cells demonstrates antibody specificity. Immunofluorescence of Phospho-Aurora A (Thr288) using with Phospho-Aurora A (Thr288) Monoclonal Antibody (F.131.2) (Product # MA5-14904) shows expression at the spindle poles in mitotic cells, as compared to no expression in resting cells of MCF7. {RE}



Phospho-Aurora A (Thr288) Antibody (MA5-14904) in ICC/IF
Immunofluorescence analysis of Phospho-Aurora A (Thr288) was performed using 70% confluent log phase MCF7 cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 15 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with Phospho-Aurora A (Thr288) Monoclonal Antibody (F.131.2) (Product # MA5-14904) at 1:250 dilution in 0.1% BSA, incubated at 4 degree Celsius overnight and then labeled with Goat anti-Mouse IgG (H+L) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A28175) for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with ProLong™ Diamond Antifade Mountant with DAPI (Product # P36962). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing localization to spindle poles in dividing cells. Panel e represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.



[View more figures on thermofisher.com](https://www.thermofisher.com)

Western Blot (2)

Nature communications CoA synthase regulates mitotic fidelity via CBP-mediated acetylation. "Published figure using Phospho-Aurora A (Thr288) monoclonal antibody (Product # MA5-14904) in Western Blot" Authors: Lin CC,Kitagawa M,Tang X,Hou MH,Wu J,Qu DC,Srinivas V,Liu X,Thompson JW,Mathey-Prevot B,Yao TP, Lee SH,Chi JT	Year 2018
Nature communications A FRET biosensor reveals spatiotemporal activation and functions of aurora kinase A in living cells. "Published figure using Phospho-Aurora A (Thr288) monoclonal antibody (Product # MA5-14904) in Western Blot" Authors: Bertolin G,Sizaire F,Herbomel G,Reboutier D,Prigent C,Tramier M	Year 2016 Species Human Dilution 1:2000

Immunocytochemistry (1)

Nature communications LPA signaling acts as a cell-extrinsic mechanism to initiate cilia disassembly and promote neurogenesis. "MA5-14904 was used in Immunocytochemistry to investigate how lysophosphatidic acid, a multifunctional bioactive phospholipid, acts as a physiological extracellular factor to initiate cilia disassembly and promote neurogenesis." Authors: Hu HB,Song ZQ,Song GP,Li S,Tu HQ,Wu M,Zhang YC,Yuan JF,Li TT,Li PY,Xu YL,Shen XL,Han QY,Li AL, Zhou T,Chun J,Zhang XM,Li HY	Year 2021 Species Human
---	---

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.