

# CD206 Monoclonal Antibody (MR5D3), Biotin

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2a
Class	Monoclonal
Type	Antibody
Clone	MR5D3
Conjugate	Biotin
Immunogen	Chimaeric CRD4-7-Fc protein.
Form	Liquid
Concentration	0.1 mg/mL
Purification	Protein G
Storage buffer	PBS with 1% BSA
Contains	0.09% sodium azide
Storage conditions	4°C or -20°C if preferred
RRID	AB_2538347


Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	Neat-1:10	-

## Product Specific Information

CD206 is expressed weakly at the cell surface. Staining may be increased following membrane permeabilization. For FACS analysis, use 10 µL of the suggested working dilution to label 1x10<sup>6</sup> cells in 100 µL.


Rat anti mouse CD206 antibody, clone MR5D3 recognizes the mouse mannose receptor, a approximately 175 kDa type 1 membrane glycoprotein that is also known as CD206.

## Product Images For CD206 Monoclonal Antibody (MR5D3), Biotin




### CD206 Antibody (MA5-16869) in IHC

Immunohistochemistry was performed on mouse lymph node tissues. Samples were probed with a Monoclonal Mannose Receptor/CD206 antibody (Product # MA5-16869) and stained with Immunoperoxidase, followed by horseradish peroxidase conjugated Goat anti Rat IgG antibody.



### CD206 Antibody (MA5-16869) in IHC

Immunohistochemistry was performed on mouse lymph node tissues. Samples were probed with a Monoclonal Mannose Receptor/CD206 antibody (Product # MA5-16869) and stained with Immunoperoxidase, followed by horseradish peroxidase conjugated Goat anti Rat IgG antibody.



### CD206 Antibody (MA5-16869) in IHC

Immunohistochemistry was performed on mouse lymph node tissues. Samples were probed with a Monoclonal Mannose Receptor/CD206 antibody (Product # MA5-16869) and stained with Immunoperoxidase, followed by horseradish peroxidase conjugated Goat anti Rat IgG antibody.

[View more figures on thermofisher.com](https://www.thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.