

CD45RA Monoclonal Antibody (OX-33), Biotin

| Product Details | |
|--------------------|--|
| Size | 100 µg |
| Species Reactivity | Rat |
| Host/Isotope | Mouse / IgG1 |
| Class | Monoclonal |
| Type | Antibody |
| Clone | OX-33 |
| Conjugate | Biotin |
| Immunogen | Rat purified spleen L-CA |
| Form | Liquid |
| Concentration | 0.1 mg/mL |
| Purification | Protein G |
| Storage buffer | PBS with 4-5mg/mL BSA |
| Contains | 0.02% sodium azide |
| Storage Conditions | Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles. |
| RRID | AB_2538868 |


| Applications | Tested Dilution | Publications |
|---|--------------------------------|--------------|
| Flow Cytometry (Flow) | 0.5 µg/1x10 ⁶ cells | - |
| Immunohistochemistry (Frozen) (IHC (F)) | Assay Dependent | - |
| Immunohistochemistry (Paraffin) (IHC (P)) | Assay Dependent | - |

Product Specific Information

MA5-17478 targets CD45RA/B in FACS, IHC (F), and IHC (P) applications and shows reactivity with Rat samples.


The MA5-17478 immunogen is rat purified spleen L-CA.

Product Images For CD45RA Monoclonal Antibody (OX-33), Biotin



CD45RA Antibody (MA5-17478) in Flow

Flow cytometric analysis of Lymph Node cells stained using anti-CD45RA/B Monoclonal Antibody (Product # MA5-17478) at a 0.5 µg/10⁶ cells dilution. The Isotype control was a Biotin Mouse IgG1



CD45RA Antibody (MA5-17478) in Flow

Flow cytometric analysis of Wistar rat splenocytes stained using a CD45RA/B monoclonal antibody (Product # MA5-17478) (filled histogram) or mouse IgG1, Kappa isotype control (open histogram).

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.