

TECK Monoclonal Antibody (89818)

Product Details

Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2B
Class	Monoclonal
Type	Antibody
Clone	89818
Conjugate	Unconjugated
Immunogen	E. coli-derived recombinant mouse CCL25/TECK Gln24-Asn144
Form	Lyophilized
Concentration	0.5 mg/mL
Purification	Protein A/G
Storage buffer	PBS with 5% trehalose
Contains	No Preservative
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2610309

Applications	Tested Dilution	Publications
Western Blot (WB)	1 µg/mL	-
Neutralization (Neu)	1.5-6.0 µg/mL	-


Product Specific Information

In direct ELISAs, no cross-reactivity with recombinant mouse (rm) CCL1, 2, 3, 4, 5, 6, 7, 9, 11, 12, 17, 19, 20, 21, 22 or 24, recombinant human (rh) CCL2, 3, 5, 7, 8, 11, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25 or 26, or recombinant rat (rr) CCL20 is observed.

Reconstitute at 0.5 mg/mL in sterile PBS.

Endotoxin level is <0.10 EU per 1 µg of the antibody by the LAL method.

Product Images For TECK Monoclonal Antibody (89818)



TECK Antibody (MA5-23847) in Neu
Neutralization of TECK in human CCR9. Samples were incubated in TECK monoclonal antibody (Product # MA5-23847). Recombinant Mouse CCL25/TECK chemoattracts the BaF3 mouse pro,B cell line transfected with human CCR9 in a dose-dependent manner (orange line). The amount of cells that migrated through to the lower chemotaxis chamber was measured by Resazurin. Chemotaxis elicited by Recombinant Mouse CCL25/TECK (1.6 μg/mL) is neutralized (green line) by increasing concentrations of Mouse CCL25/TECK Monoclonal Antibody. The ND50 is typically 1.5 , 6.0 μg/mL.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.