

# CD178 Polyclonal Antibody

Product Details	
Size	500 µL
Published Species	Rat, Human, Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	A synthetic peptide derived from N-terminal of human Fas ligand
Form	Liquid
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_11000608

Applications	Tested Dilution	Publications
Western Blot (WB)	2-4 µg/mL	-
Immunohistochemistry (IHC)	-	5 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:50-1:100	-
Immunohistochemistry (Frozen) (IHC (F))	1:100	-
Immunocytochemistry (ICC/IF)	1:100 - 1:200	-

## Product Specific Information

PA5-16746 targets Fas Ligand in IHC (P) and WB applications and shows reactivity with Human, mouse, and Rat samples.

The PA5-16746 immunogen is a synthetic peptide derived from N-terminal of human Fas ligand.

Immunohistochemistry (5)

<p>Food and chemical toxicology : an international journal published for the British Industrial Biological Research Association</p> <p><b>Propolis attenuates doxorubicin-induced testicular toxicity in rats.</b></p> <p>"PA5-16746 was used in immunohistochemistry to study the mechanism by which an extract of propolis protects against rat testicular toxicity induced by doxorubicin treatment"</p> <p>Authors: Rizk SM,Zaki HF,Mina MA</p>	<p>Year 2014</p> <p>Species Rat</p>
<p>Molecular vision</p> <p><b>Assessment of ultraviolet B-blocking effects of weekly disposable contact lenses on corneal surface in a mouse model.</b></p> <p>"PA5-16746 was used in immunohistochemistry to study the ability of different weekly disposable contact lenses to protect against UVB irradiation using a murine corneal surface model"</p> <p>Authors: Lin DP,Chang HH,Yang LC,Huang TP,Liu HJ,Chang LS,Lin CH,Chen BY</p>	<p>Year 2013</p> <p>Species Mouse</p> <p>Dilution 1:50</p>

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.