

Adenosine Kinase Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Published Species	Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant fragment corresponding to a region within amino acids 146 and 362 of Human Adenosine kinase
Form	Liquid
Concentration	0.28 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7, with 1% BSA, 20% glycerol
Contains	0.025% ProClin 300
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2544875

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:3,000	4 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:100-1:1,000	-
Immunocytochemistry (ICC/IF)	1:100-1:1,000	-

Product Specific Information

Recommended positive controls: A431, HepG2, HeLa, mouse liver, rat liver.


Predicted reactivity: Mouse (89%), Rat (87%), Chicken (83%), Rhesus Monkey (99%), Bovine (93%).

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For Adenosine Kinase Polyclonal Antibody


Adenosine Kinase Antibody (PA5-27399)

Antibody specificity was demonstrated by siRNA mediated knockdown of target protein. A431 cells were transfected with Adenosine Kinase siRNA and reduction of signal was observed in Western Blot using Adenosine Kinase Polyclonal Antibody (Product # PA5-27399). {KD}




Adenosine Kinase Antibody (PA5-27399) in WB

Western blot analysis was performed on whole cell extracts (30 µg lysate) of A549 (Lane 1), A-431 (Lane 2), Hep G2 (Lane 3), MCF7 (Lane 4), tissue extracts (30 µg lysate) of Mouse Liver (Lane 5), Rat Liver (Lane 6), Mouse Kidney (Lane 7) and Rat Kidney (Lane 8). The blot was probed with Anti-Adenosine Kinase Polyclonal Antibody (Product # PA5-27399, 1:1,000 dilution) and detected by chemiluminescence using Goat anti-Rabbit IgG (Heavy Chain) Superclonal™ Secondary Antibody, HRP conjugate (Product # A27036, 0.25 µg/mL, 1:4,000 dilution). A 56 kDa band corresponding to Adenosine Kinase was detected across the cell lines and tissues tested.



Adenosine Kinase Antibody (PA5-27399) in ICC/IF

Immunofluorescence analysis of Adenosine Kinase was performed using 70% confluent log phase PC-3 cells. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 15 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with Adenosine Kinase Polyclonal Antibody (Product # PA5-27399) at 5 µg/mL in 0.1% BSA, incubated at 4 degree Celsius overnight and then labeled with Goat anti-Rabbit IgG (Heavy Chain) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A27034) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with ProLong™ Diamond Antifade Mountant with DAPI (Product # P36962). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing cytoplasmic localization. Panel e represents control cells with no primary antibody to assess background. The images were captured at 60X magnification.



View more figures on thermofisher.com

4 References

Western Blot (4)

Cellular and molecular neurobiology

Role of Adenosine Kinase in Sphingosine-1-Phosphate Receptor 1-Induced Mechano-Hypersensitivities.

"PA5-27399 was used in Western Blot to show that SEW287-induced behavioral hypersensitivity is associated with increased expression of ADK in astrocytes of the dorsal horn of the spinal cord."

Authors: Lauro F,Giancotti LA,Kolar G,Harada CM,Harmon TA,Garrett TJ,Salvemini D

Year
2022

Species
Rat

Dilution
1:1000

International journal of molecular sciences

Adenosine Kinase Isoforms in the Developing Rat Hippocampus after LiCl/Pilocarpine Status Epilepticus.

"Published figure using Adenosine Kinase polyclonal antibody (Product # PA5-27399) in Western Blot"

Authors: Fábrega P,Uttl L,Kubová H,Tsenov G,Mareš P

Year
2022

Species
Rat

Dilution
1:3000

[View more WB references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.