

Arp3 Polyclonal Antibody

Product Details	
Size	100 µL
Species	Human, Mouse, Rat
Published Species	Bovine
Expression System	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant protein fragment corresponding to a region within amino acids 39 and 212 of Human Arp3
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7, with 1% BSA, 20% glycerol
Contains	0.01% thimerosal
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2547828

Applications	Tested Dilution	Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:100-1:1000	-
Western Blot (WB)	1:500-1:3000	1 Publication


Product Specific Information

Recommended positive controls: Jurkat.

Predicted reactivity: Mouse (100%), Rat (100%), Zebrafish (98%), Xenopus laevis (99%), Pig (99%), Chicken (99%), Chimpanzee (100%), Bovine (100%).


Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Advanced Verification Data



Arp3 Antibody (PA5-30354)


Antibody specificity was demonstrated by detection of differential basal expression of the target across tissues tested owing to their inherent genetic constitution. Relative expression of Arp3 was observed in Mouse and Rat Thymus in comparison to Mouse and Rat Skeletal Muscle using Anti-Arp3 Polyclonal antibody (Product # PA5-30354) in Western Blot. Relative expression validation info.



Arp3 Antibody (PA5-30354)

Antibody specificity was demonstrated by siRNA mediated knockdown of target protein. MCF-7 cells were transfected with Arp3 siRNA and a decrease in signal intensity was observed in western blot application using Anti-Arp3 Polyclonal Antibody (Product # PA5-30354). Knockdown validation info.

Product Images For Arp3 Polyclonal Antibody



Arp3 Antibody (PA5-30354) in IHC (P)

Immunohistochemical analysis of Arp3 in paraffin-embedded gastric carcinoma using an Arp3 polyclonal antibody (Product # PA5-30354) at a dilution of 1:500.

View more figures on thermofisher.com

Western Blot (1)

PloS one

Comparative 2D-DIGE proteomic analysis of bovine mammary epithelial cells during lactation reveals protein signatures for lactation persistency and milk yield.

"PA5-30354 was used in western blot to use 2D-DIGE and mass spectrometry to identify the protein changes in mammary epithelial cells"

Authors: Janjanam J,Singh S,Jena MK,Varshney N,Kola S,Kumar S,Kaushik JK,Grover S,Dang AK,Mukesh M,Prakash BS,Mohanty AK

Species
Bovine

Dilution
1:1000

Year
2015

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.