

TGF beta-3 Polyclonal Antibody

Product Details	
Size	500 µL
Species Reactivity	Human, Mouse, Rabbit, Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide derived from C-terminus of the precursor form of human TGFbeta3
Form	Liquid
Concentration	1.0 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.6, with 1% BSA
Contains	0.1% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2550093


Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	-
Immunohistochemistry (Paraffin) (IHC (P))	1:100	-
Immunocytochemistry (ICC/IF)	5 µg/mL	-

Product Specific Information

This antibody is predicted to react with chicken, canine, mouse, porcine and rat based on sequence homology.


Heat-mediated antigen retrieval is recommended prior to staining, using a 10mM citrate buffer, pH 6.0, for 10 minutes followed by cooling at room temperature for 20 min. Following antigen retrieval, incubate samples with primary antibody for 10 min at room temperature. A suggested positive control is placenta tissue.

Advanced Verification Data



TGF beta-3 Antibody (PA5-32630)


Antibody specificity was demonstrated by detection of differential basal expression of the target across the cell lines and tissues tested owing to their inherent genetic constitution. Relative expression of Transforming growth factor beta-3 pro protein was observed in Mouse and Rat Heart as compared to Mouse and Rat Ovary using Anti-TGF beta-3 Polyclonal Antibody (Product # PA5-32630) in Western Blot. Relative expression validation info.



TGF beta-3 Antibody (PA5-32630)

Antibody specificity was demonstrated by siRNA mediated knockdown of target protein. MCF7 cells were transfected with Transforming growth factor beta-3 pro protein siRNA and decrease in signal intensity was observed in Western Blot application using Anti-TGF beta-3 Polyclonal Antibody (Product # PA5-32630). Knockdown validation info.

Product Images For TGF beta-3 Polyclonal Antibody



TGF beta-3 Antibody (PA5-32630) in IHC

Immunohistochemical analysis of Transforming Growth Factor beta3 using anti-Transforming Growth Factor beta3 Polyclonal Antibody (Product # PA5-32630) in Placenta Tissue. The recommended dilution for this antibody in immunohistochemistry applications is 1:100.

View more figures on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.