

Aquaporin 1 Recombinant Rabbit Monoclonal Antibody (JM10-98)

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Published Species	Mouse
Host/Isotype	Rabbit / IgG
Expression system	HEK293 cells
Class	Recombinant Monoclonal
Type	Antibody
Clone	JM10-98
Conjugate	Unconjugated
Immunogen	Synthetic peptide within Human AQP1 aa 245-269
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	TBS, pH 7.4, with 40% Glycerol, 0.05% BSA
Contains	0.05% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2809870

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:2,000	-
Immunohistochemistry (IHC)	-	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	1:50-1:1000	-
Immunocytochemistry (ICC/IF)	1:50-1:200	-


Product Specific Information

Recombinant rabbit monoclonal antibodies are produced using in vitro expression systems. The expression systems are developed by cloning in the specific antibody DNA sequences from immunoreactive rabbits. Then, individual clones are screened to select the best candidates for production. The advantages of using recombinant rabbit monoclonal antibodies include: better specificity and sensitivity, lot-to-lot consistency, animal origin-free formulations, and broader immunoreactivity to diverse targets due to larger rabbit immune repertoire.

Product Images For Aquaporin 1 Recombinant Rabbit Monoclonal Antibody (JM10-98)


Aquaporin 1 Antibody (MA5-32593) in WB

Western blot was performed using Anti-Aquaporin 1 Recombinant Rabbit Monoclonal Antibody (JM10-98) (Product # MA5-32593) and a 40 kDa band corresponding to AQP1 was observed across cell lines tested and increased upon treatment in MCF7. Membrane enriched extracts (30 µg lysate) of HT-29 (Lane 1), U-2 OS (Lane 2), MCF7 (Lane 3), MCF7 treated with TGF-beta (10 ng/mL for 72 hr) (Lane 4) and ACHN (Lane 5) were electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (1:500 dilution) and detected by chemiluminescence with Goat anti-Rabbit IgG (Heavy Chain), Superclonal™ Recombinant Secondary Antibody, HRP (Product # A27036, 1:4,000 dilution) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using Novex® ECL Chemiluminescent Substrate Reagent Kit (Product # WP20005).




Aquaporin 1 Antibody (MA5-32593)

Altered expression of proteins upon cell treatment demonstrates antibody specificity. Western blot using Aquaporin 1 Recombinant Rabbit Monoclonal Antibody (JM10-98) (Product # MA5-32593), shows increased expression of proteins in MCF7 cells upon TGF-beta treatment. {TM}



Aquaporin 1 Antibody (MA5-32593) in WB

Western blot analysis of Aquaporin 1 in different lysates using a Monoclonal antibody (Product #MA5-32593) at a dilution of 1:500. Positive control: Line 1: Hela, Line 2: Jurkat, Line 3: Human kidney.



View more figures on thermofisher.com

 1 Reference

Immunohistochemistry (1)

Nature communications		Year 2022
Constitutive activation of canonical Wnt signaling disrupts choroid plexus epithelial fate.		Species Mouse
"MA5-32593 was used in Immunohistochemistry to study the presence of molecules downstream of canonical Wnt signaling in vivo at embryonic stages in the human and mouse choroid plexus."		Dilution 1:200
Authors: Parichha A,Suresh V,Chatterjee M,Kshirsagar A,Ben-Reuven L,Olender T,Taketo MM,Radosevic V,Bobic-Rasonja M,Trnski S,Holtzman MJ,Jovanov-Milosevic N,Reiner O,Tole S		

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.