

TGFBR2 Polyclonal Antibody

Product Details	
Size	100 µl
Species Reactivity	Human, Mouse, Rat
Host/Isotope	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide corresponding to amino acids 220-300 of human TGF beta RII
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.2, with 50% glycerol
Contains	0.02% sodium azide
Storage Conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2553377


Applications	Tested	Dilution	Published
Immunohistochemistry (Paraffin) (IHC (P))	✓	1:50-1:200	
Western Blot (WB)	✓	1:1000	

Product Specific Information

This antibody detects endogenous protein at a molecular weight of 65 kDa.

Purity is >95% by SDS-PAGE.

Product Images For TGFBR2 Polyclonal Antibody





TGFBR2 Antibody (PA5-36115) in IHC (P)

Immunohistochemical analysis of TGF beta Receptor II in paraffin-embedded human colorectal carcinoma using TGF beta Receptor II polyclonal antibody (Product # PA5-36115) at a dilution of 1:50.

TGFBR2 Antibody (PA5-36115) in WB

Western blot analysis was performed on membrane enriched extracts (30 µg lysate) of HT-29 (Lane 1), SW480 (Lane 2), HCT 116 (Lane 3), Hep G2 (Lane 4), HeLa (Lane 5), NIH/3T3 (Lane 6) and MDA-MB-231 (Lane 7). The blot was probed with Anti-TGFBR2 Polyclonal Antibody (Product # PA5-36115, 1:1000 dilution) and detected by chemiluminescence using Goat anti-Rabbit IgG (H+L) Superclonal™ Secondary Antibody, HRP conjugate (Product # A27036, 0.25 µg/mL, 1:4000 dilution). A 65 kDa band corresponding to TGFBR2 was observed across the cell lines tested. Apart from the desired band, 70 kDa band corresponding to the glycosylated form of TGFBR2 was detected in SW480 and MDA-MB-231 cell line.



TGFBR2 Antibody (PA5-36115) in WB

Western blot analysis of TGF beta Receptor II using TGF beta Receptor II polyclonal antibody (Product # PA5-36115) at a dilution of 1:500. Lane 1: A549 whole cell lysate, Lane 2: NIH-3T3 whole cell lysate, Lane 3: H9C2 whole cell lysate.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.