

UGT8 Polyclonal Antibody


Product Details	
Size	400 µL
Species Reactivity	Human, Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	KLH conjugated synthetic peptide between 366-393 amino acids from the Central region of human UGT8.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A, Antigen affinity chromatography
Storage buffer	PBS
Contains	0.09% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2633709

Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	-
Immunohistochemistry (IHC)	-	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	1:10-1:50	-

Product Specific Information


Predicted to react with rat based on sequence homology.

Product Images For UGT8 Polyclonal Antibody




UGT8 Antibody (PA5-48251) in IHC (P)

Immunohistochemical analysis of UGT8 in formalin fixed and paraffin embedded human brain tissue. Samples were probed with a UGT8 antibody (Center) (Product # PA5-48251) followed by peroxidase conjugation of the secondary antibody and DAB staining.



UGT8 Antibody (PA5-48251) in WB

Western blot analysis of UGT8 in human heart lysates (20µg). Samples were probed with a Anti-UGT8 antibody (Center) (Product # PA5-48251) at 1:2000 dilution, followed by Secondary Goat Anti-Rabbit IgG, (H+L), Peroxidase conjugated at 1/10000 dilution. Predicted band size : 61 kDa. Blocking/Dilution buffer: 5% NFDM/TBST.



UGT8 Antibody (PA5-48251) in WB

Western blot analysis of UGT8 in mouse cerebellum tissue lysates (35 µg/lane). Samples were probed with a UGT8 antibody (Center) (Product # PA5-48251).

[View more figures on thermofisher.com](https://thermofisher.com)

Immunohistochemistry (1)

Frontiers in oncology	Year 2022
Exploration of Lipid Metabolism in Gastric Cancer: A Novel Prognostic Genes Expression Profile.	
"Published figure using UGT8 polyclonal antibody (Product # PA5-48251) in Immunohistochemistry"	
Authors: Xiong Z,Lin Y,Yu Y,Zhou X,Fan J,Rog CJ,Cai K,Wang Z,Chang Z,Wang G,Tao K,Cai M	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.