

HSP90 Monoclonal Antibody (8D3), APC

Product Details	
Size	200 µg
Host/Isotype	Mouse / IgM
Class	Monoclonal
Type	Antibody
Clone	8D3
Conjugate	APC
Excitation/Emission Max	651/660 nm
Immunogen	Ah receptor (Aryl hydrocarbon receptor)
Form	Liquid
Concentration	1 mg/mL
Storage conditions	4° C

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC/IF)	1:100	-
Immunoprecipitation (IP)	1:1,000	-

Product Specific Information

Goat anti-mouse IgM was used to bind 25 µl of protein G-Sepharose. MA5-45106 IgM from 0.5 ml of high speed supernatant medium was loaded onto the IgG resin and incubated with 100 µl of rabbit reticulocyte lysate for 30 min. at 30C. After washing (4X1 ml), bound proteins were resolved on SDS PAGE, including HSP90, HSP70 and Hop. |Detects 90kDa. Co-immunoprecipitates HSP90 complexes, including HSP70, Hop, Ah receptors, glucocorticoid receptors, heme-regulated eukaryotic initiation factor 2 alpha (eIF-2 alpha) kinase (HRI).

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.