

HSP27 Monoclonal Antibody (5D12-A12), FITC

Product Details	
Size	200 µg
Species Reactivity	Human
Host/Isotype	Mouse / IgG2b, kappa
Class	Monoclonal
Type	Antibody
Clone	5D12-A12
Conjugate	FITC
Excitation/Emission Max	498/517 nm
Immunogen	Full length human HSP27
Form	Liquid
Concentration	1 mg/mL
Purification	Protein G
Storage buffer	9.44mM PBS/9.1mM sodium bicarbonate, pH 7.2, with 581mM DMSO, 123mM ethanolamine
Contains	no preservative
Storage conditions	4° C, store in dark

Applications	Tested Dilution	Publications
Western Blot (WB)	1:2,000	-
Immunohistochemistry (IHC)	Assay-dependent	-
Immunocytochemistry (ICC/IF)	1:100	-
ELISA (ELISA)	Assay-dependent	-
Immunoprecipitation (IP)	Assay-dependent	-


Product Specific Information

0.5 µg/mL of MA5-45206 was sufficient for detection of HSP27 in 10 µg of HeLa lysate by colorimetric immunoblot analysis using Goat anti-mouse IgG:HRP as the secondary antibody. Detects approximately 27kDa. Has no cross-reactivity to Alpha B crystallin. Very limited cross-reactivity to other species.

Product Images For HSP27 Monoclonal Antibody (5D12-A12), FITC


HSP27 Antibody (MA5-45206) in ICC/IF

Immunocytochemistry/Immunofluorescence analysis using human heat shocked cervical cancer cells. Fixation involved 2% Formaldehyde for 20 min at RT. Samples were incubated with Hsp27 monoclonal antibody (Product # MA5-45206) at 1:100 for 12 hours at 4°C, followed by FITC Goat Anti-Mouse (green) at 1:200 for 2 hours at RT. Counterstain used was DAPI (blue) nuclear stain at 1:40,000 for 2 hours at RT. Localization: Cytoplasm. Nucleus. Magnification: 100x. (A) DAPI (blue) nuclear stain. (B) Anti-Hsp27 antibody. (C) Composite. Heat Shocked at 42°C for 1h.




HSP27 Antibody (MA5-45206) in ICC/IF

Immunocytochemistry/Immunofluorescence analysis using human heat shocked cervical cancer cells. Fixation involved 2% Formaldehyde for 20 min at RT. Samples were incubated with Hsp27 monoclonal antibody (Product # MA5-45206) at 1:100 for 12 hours at 4°C, followed by FITC Goat Anti-Mouse (green) at 1:200 for 2 hours at RT. Counterstain used was DAPI (blue) nuclear stain at 1:40,000 for 2 hours at RT. Localization: Cytoplasm. Nucleus. Magnification: 20x. (A) DAPI (blue) nuclear stain. (B) Anti-Hsp27 antibody. (C) Composite. Heat Shocked at 42°C for 1h.



HSP27 Antibody (MA5-45206) in ICC/IF

Immunocytochemistry/Immunofluorescence analysis using HaCaT cells. Fixation involved Cold 100% methanol for 10 minutes at -20°C. Samples were incubated with Hsp27 monoclonal antibody (Product # MA5-45206) at 1:100 for 1 hour at RT, followed by FITC Goat Anti-Mouse (green) at 1:50 for 1 hour at RT. Localization: Dull heterogeneous staining, some perinuclear, some nuclear and some cytoplasmic staining.



View more figures on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.