

Leptin Receptor Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Mouse, Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide corresponding to residues K(577) E I Q W K T H E V F D A K S K S A(594) of the extracellular domain of rat OB-R.
Form	Liquid
Concentration	10 mg/mL
Purification	Ammonium sulfate precipitation
Storage buffer	PBS
Contains	0.05% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2296991

Applications	Tested Dilution	Publications
Western Blot (WB)	1:2,000	7 Publications
Immunohistochemistry (IHC)	-	2 Publications
Neutralization (Neu)	-	1 Publication


Product Specific Information

PA1-053 detects leptin (OB-R) from human, mouse, and rat tissues.

PA1-053 has been successfully used in Western blot procedures. By Western blot, this antibody detects an ~100 kDa and ~125 kDa protein representing the short and long forms of OB-R from mouse brain extract. This antibody also detects two smaller, unrelated proteins of ~31 kDa and 35 kDa which are unable to be competed with the peptide in mouse liver extract.

The PA1-053 immunogen is a synthetic peptide corresponding to residues K(577) E I Q W K T H E V F D A K S K S A(594) of the extracellular domain of rat OB-R. This sequence is completely conserved in mouse OB-R. PA1-053 immunizing peptide (Cat. # PEP-014) is available for use in neutralization and control experiments.

Fig. 1



Leptin Receptor Antibody (PA1-053) in WB
Western blot detection of both short and long forms of OB-R from mouse lung tissue extract using Product # PA1-053.

Western Blot (7)

<p>Endocrinology</p> <p>Renal Metabolic Programming Is Linked to the Dynamic Regulation of a Leptin-Klf15 Axis and Akt/AMPK Signaling in Male Offspring of Obese Dams.</p> <p>"PA1-053 was used in Western Blotting to study the impact of maternal obesity on renal-intrinsic insulin and adipocytokine signalling and on renal function and structure."</p> <p>Authors: Kasper P,Vohlen C,Dinger K,Mohr J,Hucklenbruch-Rother E,Janoschek R,Köth J,Matthes J,Appel S,Dötsch J,Alejandro Alcazar MA</p>	<p>Year 2017</p> <p>Species Mouse</p> <p>Dilution 1:1000</p>
<p>Journal of Alzheimer's disease : JAD</p> <p>Leptin reduces pathology and improves memory in a transgenic mouse model of Alzheimer's disease.</p> <p>"PA1-053 was used in western blot to investigate the effect of leptin treatment on histopathology and memory capability in Alzheimer disease model"</p> <p>Authors: Greco SJ,Bryan KJ,Sarkar S,Zhu X,Smith MA,Ashford JW,Johnston JM,Tezapsidis N,Casadesus G</p>	<p>Year 2010</p> <p>Species Mouse</p> <p>Dilution 1:1000</p>

[View more WB references on thermofisher.com](#)

Immunohistochemistry (2)

<p>Journal of neurochemistry</p> <p>Dysregulation of leptin signaling in Alzheimer disease: evidence for neuronal leptin resistance.</p> <p>"Published figure using Leptin Receptor polyclonal antibody (Product # PA1-053) in Immunohistochemistry"</p> <p>Authors: Bonda DJ,Stone JG,Torres SL,Siedlak SL,Perry G,Kryscio R,Jicha G,Casadesus G,Smith MA,Zhu X,Lee HG</p>	<p>Year 2014</p> <p>Species Human</p>
<p>Biology of reproduction</p> <p>Expression of leptin and its receptor in the murine ovary: possible role in the regulation of oocyte maturation.</p> <p>"PA1-053 was used in immunohistochemistry to investigate the distribution of leptin and its receptor in whole tissue sections of the mouse ovary as well as the corresponding effect on mouse oocyte maturation and changes in oocyte cAMP levels"</p> <p>Authors: Ryan NK,Woodhouse CM,Van der Hoek KH,Gilchrist RB,Armstrong DT,Norman RJ</p>	<p>Year 2002</p> <p>Species Mouse</p> <p>Dilution 1:100</p>

More applications with references on thermofisher.com

Neu (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.