

Phospho-Caveolin 2 (Tyr19) Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Mouse, Human
Published Species	Mouse
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic phosphopeptide corresponding to residues M(14) A D D A (pY) S H H S G C(25) of mouse CAV2.
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS with 1mg/mL BSA
Contains	0.05% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_2072311

Applications	Tested Dilution	Publications
Western Blot (WB)	2 µg/mL	1 Publication
Immunocytochemistry (ICC/IF)	1-2 µg/mL	-
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

PA1-060 detects phospho-caveolin-2 Y19 from human and mouse samples.


PA1-060 has been successfully used in Western blot and immunofluorescence procedures. By Western blot, this antibody detects an ~21 kDa protein representing phospho-caveolin-2 Y19 from extract from COS-7 cells transiently transfected with the mouse caveolin-2 gene. Immunofluorescent staining of phospho-caveolin-2 Y19 in NIH 3T3 cells using PA1-060 results in a distinct punctate staining pattern at the cell periphery.

The PA1-060 immunogen is a synthetic phosphopeptide corresponding to residues M(14) A D D A (pY) S H H S G C(25) of mouse CAV2. This peptide (Cat. # PEP-180) is available for use in neutralization and control experiments.

Product Images For Phospho-Caveolin 2 (Tyr19) Polyclonal Antibody


Phospho-Caveolin 2 (Tyr19) Antibody (PA1-060) in ICC/IF

Immunofluorescence analysis of Phospho-Caveolin 2 pTyr19 was done on 70% confluent log phase A-375 cells. The cells were fixed with 4% paraformaldehyde for 15 minutes, permeabilized with 0.25% Triton™ X-100 for 10 minutes, and blocked with 5% BSA for 1 hour at room temperature. The cells were labeled with Phospho-Caveolin 2 pTyr19 Rabbit Polyclonal Antibody (Product # PA1-060) at 1 µg/mL in 1% BSA and incubated for 3 hours at room temperature and then labeled with Goat anti-Rabbit IgG (Heavy Chain) Superclonal™ Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A27034) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Alexa Fluor® 555 Rhodamine Phalloidin (Product # R415, 1:300). Panel d is a merged image showing membranous localization. Panel e is a no primary antibody control. The images were captured at 60X magnification.



Phospho-Caveolin 2 (Tyr19) Antibody (PA1-060) in ICC/IF

Immunofluorescent analysis of Phospho-Caveolin 2 pTyr19 (green) showing staining in the cytoplasm and nucleus of HUVEC cells treated with 100µM pervanadate (left) and untreated HUVEC cells (right). Formalin-fixed cells were permeabilized with 0.1% Triton X-100 in TBS for 5-10 minutes and blocked with 3% BSA-PBS for 30 minutes at room temperature. Cells were probed with a Phospho-Caveolin 2 pTyr19 polyclonal antibody (Product # PA1-060) in 3% BSA-PBS at a dilution of 1:20 and incubated overnight at 4°C in a humidified chamber. Cells were washed with PBST and incubated with a DyLight-conjugated secondary antibody in PBS at room temperature in the dark. F-actin (red) was stained with a fluorescent red phalloidin and nuclei (blue) were stained with Hoechst or DAPI. Images were taken at a magnification of 60x.



[View more figures on thermofisher.com](#)

Western Blot (1)

Cell cycle (Georgetown, Tex.)	Year 2013
Genetic ablation of caveolin-2 sensitizes mice to bleomycin-induced injury.	Species Mouse
"Published figure using Phospho-Caveolin 2 (Tyr19) polyclonal antibody (Product # PA1-060) in Western Blot"	Dilution 1:1,000
Authors: de Almeida CJ,Jasmin JF,Del Galdo F,Lisanti MP	

Miscellaneous PubMed (1)

The Journal of biological chemistry	Year 2002
Src-induced phosphorylation of caveolin-2 on tyrosine 19. Phospho-caveolin-2 (Tyr(P)19) is localized near focal adhesions, remains associated with lipid rafts/caveolae, but no longer forms a high molecular mass hetero-oligomer with caveolin-1.	
"PA1-060 was used in immunocytochemistry and western blot to investigate the phosphorylation of caveolin 2 by c-Src"	
Authors: Lee H,Park DS,Wang XB,Scherer PE,Schwartz PE,Lisanti MP	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.