

Sheep anti-Rat IgG (H+L) Secondary Antibody, TRITC

Product Details	
Size	1 mg
Species Reactivity	Rat
Host/Isotype	Sheep / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	TRITC
Excitation/Emission Max	552/578 nm
Immunogen	Rat IgG whole molecule
Form	Liquid
Concentration	2 mg/mL
Purification	IgG fraction
Storage buffer	0.02M potassium phosphate, pH 7.2, with 0.15M NaCl, 10mg/mL BSA
Contains	0.01% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles. Store in the dark.
RRID	AB_10984808

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC/IF)	1:1,000-1:5,000	-
Flow Cytometry (Flow)	1:500-1:2500	-
Immunomicroscopy (IM)	Assay-dependent	-


Product Specific Information

Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For Sheep anti-Rat IgG (H+L) Secondary Antibody, TRITC

Rat IgG (H+L) Secondary Antibody (PA1-28639) in ICC/IF

Immunofluorescence analysis of Sheep anti-Rat IgG Secondary Antibody, TRITC was performed using A549 cells stained with alpha Tubulin (YL1/2) Rat Monoclonal Antibody (Product # MA1-80017). The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, blocked with 1% BSA for 1 hour and labeled with 2µg/mL Rat primary antibody for 3 hours at room temperature. Sheep anti-Rat IgG Secondary Antibody, TRITC (Product # PA1-28639) was used at a concentration of 4µg/mL in phosphate buffered saline containing 0.2 % BSA for 45 minutes at room temperature, for detection of alpha Tubulin in the cytoplasm (Panel a: red). Nuclei (Panel b: blue) were stained with DAPI in SlowFade® Gold Antifade Mountant (Product # S36938). F-actin was stained with Alexa Fluor® 488 Phalloidin (Product # A12379), 1:300 (Panel c: green). Panel d represents the composite image. No nonspecific staining was observed with the secondary antibody alone (panel f), or with an isotype control (panel e). The images were captured at 60X magnification.



For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.