


RIP3 Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Human, Non-human primate
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide corresponding to residues 497-510 and 298-311 of human RIP3.
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS
Contains	0.05% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_1087139


Applications	Tested Dilution	Publications
Immunocytochemistry (ICC)	1:20-1:500	-
Immunofluorescence (IF)	1:20-1:500	-
Immunohistochemistry (Paraffin) (IHC (P))	10 µg/mL	-
Western Blot (WB)	3-7 µg/mL	2 Publications

Product Images For RIP3 Polyclonal Antibody



RIP3 Antibody (PA1-41533) in IHC

Immunohistochemical analysis of RIP3 in Human pancreas tissue using a RIPK3 polyclonal antibody (Product # PA1-41533) at 10 µg/mL.



RIP3 Antibody (PA1-41533) in WB

Western blot analysis of RIP3 using a RIPK3 polyclonal antibody (Product # PA1-41533). human tissue blot probed with 5 µg/mL of a RIPK3 polyclonal antibody (Product # PA1-41533): lanes 1) brain, 2) heart, 3) small intestine, 4) kidney, 5) liver, 6) lung, 7) skeletal muscle, 8) stomach, 9) spleen, 10) ovary, 11) testis. Lane 12 is human placenta probed at 5 µg/mL and lane 13 is human Ramos cell lysate probed at 7 µg/mL. Goat anti-rabbit Ig HRP secondary antibody.

2 References

Western Blot (2)

Cell death and disease

Sorafenib tosylate inhibits directly necrosome complex formation and protects in mouse models of inflammation and tissue injury.

"Published figure using RIP3 polyclonal antibody (Product # PA1-41533) in Western Blot"

Authors: Martens S, Jeong M, Tonnus W, Feldmann F, Hofmans S, Goossens V, Takahashi N, Bräsen JH, Lee EW, Van der Veken P, Joossens J, Augustyns K, Fulda S, Linkermann A, Song J, Vandenabeele P

Species
Human

Dilution
Not Cited

Year
2017

Nature communications

Ubiquitination and degradation of the FADD adaptor protein regulate death receptor-mediated apoptosis and necroptosis.

"PA1-41533 was used in western blot to study the role of FADD adaptor protein degradation in death receptor-mediated apoptosis and necroptosis"

Authors: Lee EW, Kim JH, Ahn YH, Seo J, Ko A, Jeong M, Kim SJ, Ro JY, Park KM, Lee HW, Park EJ, Chun KH, Song J

Species
Human

Dilution
1:2000

Year
2012

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.