

MEL18 Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Human
Host/Isotope	Goat / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide sequence (KMTVNGAPVPPLT) corresponding to the C-terminus amino acids of PCGF2
Form	Liquid
Concentration	0.5 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	TBS, pH 7.3, with 0.5% BSA
Contains	0.02% sodium azide
Storage Conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_10979036


Applications	Tested	Dilution	Published
Western Blot (WB)	✓	0.3-1 µg/mL	

Product Specific Information

This antibody is predicted to react with bovine and canine based on sequence homology.

MEL18 Antibody (PA5-18163)


Altered expression of MEL18 protein upon cell treatment demonstrated antibody specificity. A treatment mediated reduction of MEL18 in AML-193 cells with Retinoic acid treatment was observed using MEL18 Polyclonal Antibody (Product # PA5-18163) in Western Bot. . Cell Treatment validation info.




Product Images For MEL18 Polyclonal Antibody

MEL18 Antibody (PA5-18163) in WB

Western blot was performed using Anti-MEL18 Goat Polyclonal Antibody (Product # PA5-18163) and 37 kDa band corresponding to MEL18 was observed across the cell lines tested and was also found to decrease upon Retinoic Acid treatment in AML-193 cell line. Uncharacterized bands at 60 was observed in Hep G2 cell line. Modified Whole cell extracts (1%SDS) (30 µg lysate) of Hep G2 (Lane 1), A549 (Lane 2), SH-SY5Y (Lane 3), HeLa (Lane 4), AML-193 (Lane 5), AML-193 treated with Retinoic Acid (10uM for 2 days) (Lane 6) and AML-193 treated with Retinoic Acid (10uM for 8 days) (Lane 7), were electrophoresed using Novex® NuPAGE® 4-12% Bis-Tris gel (Product # NP0322BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (1µg/mL) and detected by chemiluminescence Anti-Goat IgG Secondary Antibody, HRP conjugate (Product # A27014, 1:4000 dilution) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using Novex® ECL Chemiluminescent Substrate Reagent Kit (Product # WP20005).





MEL18 Antibody (PA5-18163) in WB

Western blot analysis of MEL18 by a MEL18 monoclonal antibody (Product # PA5-18163) at a concentration of 1 µg/mL. A549 (A) and PD19 (B) cell lysate (RIPA buffer, 30µg total protein per lane). Detected by chemiluminescence.

[View more figures on thermofisher.com](https://www.thermofisher.com)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.

