

SEPT6 Polyclonal Antibody

Product Details	
Size	100 µg
Species Reactivity	Human
Published Species	Human
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide sequence (DEVNAFKQRKTA) corresponding to the internal amino acids of 38961
Form	Liquid
Concentration	0.5 mg/mL
Purification	Ammonium sulfate precipitation
Storage buffer	TBS, pH 7.3, with 0.5% BSA
Contains	0.02% sodium azide
Storage conditions	-20° C, Avoid Freeze/Thaw Cycles
RRID	AB_10977982


Applications	Tested Dilution	Publications
Western Blot (WB)	0.1-1 µg/mL	-
Immunohistochemistry (IHC)	3-5 µg/mL	-
Immunocytochemistry (ICC/IF)	-	1 Publication

Product Specific Information

This antibody is predicted to react with bovine and canine based on sequence homology.


This antibody is tested in Peptide ELISA: antibody detection limit dilution 4,000.

Product Images For SEPT6 Polyclonal Antibody



SEPT6 Antibody (PA5-19024) in WB

Western blot analysis of SEPT6 using SEPT6 Polyclonal Antibody (Product # PA5-19024) (1 µg/mL) in staining of Human Testis (A), (0.1 µg/mL) Human Duodenum (B), (0.5 µg/mL) Human Kidney (C) and (0.3 µg/mL) Human Tonsil (D) lysate (35 µg protein in RIPA buffer). Detected by chemiluminescence.



SEPT6 Antibody (PA5-19024) in WB
 Western blot analysis of SEPT6 using SEPT6 Polyclonal Antibody (Product # PA5-19024) (0.1 µg/mL) in staining of Daudi (A), Jurkat (B) and MOLT4 (C) cell lysate (35 µg protein in RIPA buffer). Detected by chemiluminescence.

1 Reference

Immunocytochemistry (1)

Mediators of inflammation

UBC Mediated by SEPT6 Inhibited the Progression of Prostate Cancer.

"Published figure using SEPT6 polyclonal antibody (Product # PA5-19024) in Immunocytochemistry"

Authors: Zhang R,Yang Y,Huang H,Li T,Ye L,Lin L,Wei Y

Year
2022

Species
Human

Dilution
1:50

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.