

# Human CD25 (IL-2R alpha) Recombinant Protein, eBioscience™

## Product Details

Size	100 µg
Species	Human
Expression system	Insect cells
Amino acid sequence	Human CD25, amino acids Glu22-Gln240 (Accession # NP_000408.1)
Molecular weight	24.8 kDa
Class	Recombinant
Type	Protein
Purity	>98% by SDS-PAGE and HPLC
Endotoxin concentration	<0.1 ng/µg
Activity	ED50 = 0.5-1.5 µg; determined by the dose-dependent proliferation of CTLL-2 cells stimulated with 1 ng/mL IL-2.
Conjugate	Unconjugated
Form	Lyophilized
Storage conditions	-20°C

## Applications

## Tested Dilution

## Publications

Functional Assay (FN)	Assay-Dependent	-
Control (Ctrl)	Assay-Dependent	-

## Product Specific Information

**Description:** The human soluble IL-2 receptor alpha chain (sIL-2Ra) is generated by proteolytic cleavage of the cell-surface bound receptor on activated T cells. The IL-2Ra (also known as CD25) is expressed by early progenitors of the T and B lineage, as well as by activated mature T and B lymphocytes. By itself, CD25 binds IL-2 with low affinity. However, association with CD122 (IL-2 receptor beta chain) and CD132 (common gamma chain) results in formation of the high affinity IL-2R. CD25 plays a role in lymphocyte differentiation and activation/proliferation. sIL-2Ra has been detected in the serum of patients with autoimmune disease and leukemia. Reports have demonstrated that addition of sIL-2Ra can inhibit IL-2-mediated signaling and enhance Th17 responses.

**Applications Reported:** Recombinant human soluble IL-2Ra is biologically active and can enhance proliferation of mouse CTLL-2 cells stimulated with 1 ng/mL IL-2.

**Applications Tested:** The ED50 of this protein, as determined by increased proliferation of mouse CTLL-2 cells stimulated with 1 ng/mL IL-2, is 0.5-1.5 µg/mL.

**Source:** Insect cells (amino acids Glu22-Gln240; accession #: NP\_000408.1).

**Bioactivity:** The ED50 of this protein, as determined by increased proliferation of mouse CTLL-2 cells stimulated with 1 ng/mL IL-2, is 0.5-1.5 µg/mL.

**Endotoxin:** Less than 0.1 ng/ug cytokine as determined by the LAL assay. **Purity:** >98% as determined by SDS-PAGE and HPLC.

**Molecular Weight:** 24.8 kDa.

**Storage and handling:** For best recovery, quick spin vial prior to opening. Reconstitute in 1X PBS, pH 7.2 to a concentration of 0.1-1.0 mg/mL. Do not vortex. Use in sterile environment. Store lyophilized protein at less than or equal to -20°C. Reconstituted protein solution can be stored with carrier-protein (e.g., 0.1% BSA) at less than or equal to -20°C.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.