

# Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, FITC


Product Details	
Size	1 mg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	FITC
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Concentration	2 mg/mL
Purification	purified
Storage buffer	PBS, pH 7.5
Contains	5mM sodium azide
Storage conditions	4° C, store in dark
RRID	AB_2536524

Applications	Tested Dilution	Publications
Western Blot (WB)	-	1 Publication
Immunohistochemistry (IHC)	1-10 µg/mL	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	Assay-dependent	5 Publications
Immunohistochemistry - Free Floating (IHC (Free))	-	1 Publication
Immunocytochemistry (ICC/IF)	1-10 µg/mL	5 Publications
Flow Cytometry (Flow)	1-10 µg/mL	1 Publication
Miscellaneous PubMed (Misc)	-	509 Publications

## Product Images For Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, FITC


### Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (F-2761) in ICC/IF

A 20-second time series showing enhanced resistance to photobleaching afforded by ProLong® Gold antifade reagent. Fixed bovine pulmonary artery endothelial cells were labeled with anti- $\beta$ -tubulin (Product # A11126) and visualized with FITC-conjugated goat anti-mouse IgG (Product # F-2761). The samples were mounted in ProLong® Gold antifade reagent (Product # P36930; top) or phosphate-buffered saline (bottom). Images were acquired at 5 second intervals using a 40x/1.3 NA oil immersion objective with continuous illumination from a standard 100 watt Hg-arc lamp.




### Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (F-2761) in IHC

Representative photomicrographs of viral antigen positive cells (green) in different tissues of moribund and dead shrimp. WSSV was detected by IIF using a VP28-specific mouse monoclonal antibody and an FITC-conjugated goat-anti mouse IgG. The cells of connective tissue (CT) of the midgut were WSSV positive, while the epithelial cells (EP) were WSSV negative. Image collected and cropped by CiteAb from the following publication (<http://www.veterinaryresearch.org/content/47/1/39>), licensed under a CC BY license.



### Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (F-2761) in ICC/IF

The relative photobleaching rates of FITC and Texas Red® fluorophores with buffer alone (right series) or after treatment with the ProLong® antifade reagent (left series). Bovine pulmonary artery endothelial cells were fixed, permeabilized and labeled with Texas Red®-X phalloidin (Product # T7471), which labels F-actin, and with a mouse monoclonal anti- $\beta$ -tubulin antibody and FITC-conjugated goat anti-mouse IgG antibody (Product # F-2761), which label microtubules. Images were acquired at appropriate wavelengths using a cooled CCD camera.



View more figures on [thermofisher.com](http://thermofisher.com)

## Western Blot (1)

### Endocrinology

#### Pathogenic Phenotype of Adipogenesis and Hyaluronan in Orbital Fibroblasts From Female Graves' Orbitopathy Mouse Model.

"F2761 was used in western blot to examine the contribution of orbital fibroblasts in a mouse model of Graves' orbitopathy"

Authors: Görtz GE, Moshkelgosha S, Jesenek C, Edelmann B, Horstmann M, Banga JP, Eckstein A, Berchner-Pfannschmidt U

**Species**  
Not Applicable

**Dilution**  
5 µg/ml

**Year**  
2016

## Immunohistochemistry (2)

### Clinical and experimental immunology

#### Programmed death-1 ligands 1 and 2 expression in cutaneous squamous cell carcinoma and their relationship with tumour-infiltrating dendritic cells.

"F2761 was used in immunohistochemistry to determine PD-L1 and PD-L2 expression and dendritic cell infiltration in tumor tissue of cutaneous squamous cell carcinoma patients"

Authors: Jiao Q, Liu C, Li W, Li W, Fang F, Qian Q, Zhang X

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2017

### Diseases of aquatic organisms

#### Pathogenesis of a Thai strain of white spot syndrome virus (WSSV) in juvenile, specific pathogen-free *Litopenaeus vannamei*.

"F-2761 was used in immunohistochemistry to study *Litopenaeus vannamei* infected with white spot syndrome virus"

Authors: Escobedo-Bonilla CM, Wille M, Alday Sanz V, Sorgeloos P, Pensaert MB, Nauwynck HJ

**Species**  
Not Applicable

**Dilution**  
0.2 µg/ml

**Year**  
2007

## Immunohistochemistry (Frozen) (5)

### Journal of fish diseases

#### Effects of acute change in salinity and moulting on the infection of white leg shrimp (*Penaeus vannamei*) with white spot syndrome virus upon immersion challenge.

"F2761 was used in immunohistochemistry - frozen section to determine the effects of environmental salinity and moulting on the susceptibility of *Penaeus vannamei* to WSSV"

Authors: Van Thuong K, Van Tuan V, Li W, Sorgeloos P, Bossier P, Nauwynck H

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2016

[View more IHC \(F\) references on thermofisher.com](#)

## More applications with references on thermofisher.com

IHC (Free) (1)

ICC/IF (5)

Flow (1)

Misc (509)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.