

PKM2 Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant fragment corresponding to a region within amino acids 243 and 531 of Human Pyruvate Kinase
Form	Liquid
Concentration	0.13 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7, with 20% glycerol, 1% BSA
Contains	0.025% ProClin 300
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2546176

Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:3,000	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	1:100-1:1,000	-
Immunocytochemistry (ICC/IF)	1:100-1:1,000	-
Immunoprecipitation (IP)	1:100-1:500	-


Product Specific Information

Recommended positive controls: 293T, A431, HeLa, HepG2, mouse brain, rat brain.

Predicted reactivity: Mouse (97%), Rat (88%), Xenopus laevis (90%), Rabbit (97%), Chicken (83%), Bovine (97%).


Store product as a concentrated solution. Centrifuge briefly prior to opening the vial.

Product Images For PKM2 Polyclonal Antibody




PKM2 Antibody (PA5-28700) in ICC/IF

PKM2 Polyclonal Antibody detects PKM protein at cytoplasm by immunofluorescent analysis. Sample: HeLa cells were fixed in 4% paraformaldehyde at RT for 15 min. Green: PKM stained by PKM2 Polyclonal Antibody (Product # PA5-28700) diluted at 1:500. Blue: Fluoroshield with DAPI .



PKM2 Antibody (PA5-28700)

Antibody specificity was demonstrated by shRNA mediated knockdown of the target protein. 293T cells were transfected with PKM shRNA and decrease in signal intensity was observed in western blot application using Pyruvate kinase (PKM2) polyclonal antibody (Product # PA5-28700). {KD}



PKM2 Antibody (PA5-28700) in ICC/IF

Immunocytochemistry-Immunofluorescence analysis of PKM2 was performed in HeLa cells fixed in 4% paraformaldehyde at RT for 15 min. Green: PKM2 Polyclonal Antibody (Product # PA5-28700) diluted at 1:500. Red: alpha Tubulin, a cytoskeleton marker. Blue: Hoechst 33342 staining.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Western Blot (1)

Open medicine (Warsaw, Poland)	Year 2021
circATP2A2 promotes osteosarcoma progression by upregulating MYH9.	
"Published figure using PKM2 polyclonal antibody (Product # PA5-28700) in Western Blot"	
Authors: Cao X,Meng X,Fu P,Wu L,Yang Z,Chen H	

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.