Phospho-Caspase 9 (Tyr153) Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic phosphopeptide derived from human Caspase 9 around the phosphorylation site of Tyrosine 153
Form	Liquid
Concentration	1 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	15mM sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2553329


Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:1,000	-

Product Specific Information


This antibody detects endogenous protein at a molecular weight of 35 and 48 kDa.

Purity is >95% by SDS-PAGE.

Product Images For Phospho-Caspase 9 (Tyr153) Polyclonal Antibody



Phospho-Caspase 9 (Tyr153) Antibody (PA5-36020) in WB
Western blot analysis of Phospho-Caspase 9 pTyr153 using Phospho-Caspase 9 pTyr153 polyclonal antibody (Product # PA5-36020) at a dilution of 1:500. Lane 1: HEK293T whole cell lysate, Lane 2: Raw264.7 whole cell lysate, Lane 3: PC12 whole cell lysate.



Phospho-Caspase 9 (Tyr153) Antibody (PA5-36020) in WB
Western blot analysis of Phospho-Caspase 9 (Tyr153) in Lane 1: HEK293T whole cell lysate (40 µg), Lane 2: HEK293T treated with UV for 1h whole cell lysate (40 µg), Lane 3: HEK293T treated with UV for 6h whole cell lysate (40 µg), Lane 4: HEK293T treated with UV for 16h whole cell lysate (40 µg), Lane 5: HEK293T treated with UV for 24h whole cell lysate (40 µg). Samples were incubated with Phospho-Caspase 9 (Tyr153) polyclonal antibody (Product # PA5-36020) at a dilution of 1:500.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.