

CYP24A1 Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant protein corresponding to Human CYP24A1
Form	Liquid
Concentration	0.4 mg/mL
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2640319


Applications	Tested Dilution	Publications
Western Blot (WB)	0.04-0.4 µg/mL	-
Immunohistochemistry (IHC)	1:500-1:1,000	-
Immunocytochemistry (ICC/IF)	0.25-2 µg/mL	-

Product Specific Information

Immunogen sequence: DFLCDIYHQN RLSKKELYAA VTELQLAAVE TTANSLMWIL YNLSRNPQVQ QKLLKEIQSV LPENQVPRAE DLRNMPYLKA CLKESMRLTP SVPFTTRTLD KATVLGEYAL PKGTVLMLNT QV

Highest antigen sequence identity to the following orthologs: Mouse - 91%, Rat - 90%.

Product Images For CYP24A1 Polyclonal Antibody




CYP24A1 in Urinary bladder

CYP24A1 in Skeletal muscle




CYP24A1 Antibody (PA5-54579)

Relative expression in different tissues in IHC: Detection of differential expression levels of CYP24A1 demonstrates antibody specificity. Immunohistochemical analysis of CYP24A1 using anti-CYP24A1 Polyclonal Antibody (Product # PA5-54579), shows significant staining of CYP24A1 in human urinary bladder and shows minimal or weak staining in human skeletal muscle tissues. The relative expression levels of CYP24A1 within each tissue is shown using RNA-Seq. {RE}



CYP24A1 Antibody (PA5-54579) in ICC/IF

Immunofluorescent staining of CYP24A1 in human cell line A549 shows positivity in mitochondria. Samples were probed using a CYP24A1 Polyclonal Antibody (Product # PA5-54579).



CYP24A1 Antibody (PA5-54579)

Relative expression in western blot: Antibody specificity was demonstrated by detection of known differential basal expression of the target across tissue/cell models. Expression of CYP24A1 was observed specifically in A-549 cells and in SK-MEL-30 cells using anti-CYP24A1 Polyclonal Antibody (Product # PA5-54579) in western blot. The relative expression levels of CYP24A1 within each cell line is shown using RNA-Seq. {RE}

View more figures on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.