

DNAJB9 Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human
Published Species	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant protein corresponding to Human DNAJB9
Form	Liquid
Concentration	0.15 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.2, with 40% glycerol
Contains	0.02% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2640689


Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	1:200-1:500	3 Publications
Immunocytochemistry (ICC/IF)	0.25-2 µg/mL	-

Product Specific Information

Immunogen sequence: TLSDANRRKE YDTLGHSFT SGKGQRGSGS SFEQSFNFNF DDLFKDFGFF GQNQNTGSKK RFENHFQTRQ DG

Highest antigen sequence identity to the following orthologs: Mouse - 88%, Rat - 86%.

Product Images For DNAJB9 Polyclonal Antibody



DNAJB9 Antibody (PA5-59621) in ICC/IF
Immunofluorescent staining of DNAJB9 in human cell line BJ using a DNAJB9 Polyclonal Antibody (Product # PA5-59621) shows localization to cytosol and endoplasmic reticulum.

3 References

Immunohistochemistry (3)

Biomedicines	Year 2022
DNAJB9 Is a Reliable Immunohistochemical Marker of Fibrillary Glomerulonephritis: Evaluation of Diagnostic Efficacy in a Large Series of Kidney Biopsies.	
"Published figure using DNAJB9 polyclonal antibody (Product # PA5-59621) in Immunohistochemistry"	
Authors: Gambella A,Pitino C,Barreca A,Nocifora A,Giarin MM,Bertero L,Biancone L,Roccatello D,Papotti M,Cassoni P	
Clinical kidney journal	Year 2021
Characteristics of patients with coexisting DNAJB9-associated fibrillary glomerulonephritis and IgA nephropathy.	Species Human
"PA5-59621 was used in Immunohistochemistry to show that the diagnosis of this dual glomerulopathy requires careful evaluation of immunofluorescence findings, and electron microscopy or DNAJB9."	Dilution 1:200
Authors: Said SM,Rocha AB,Valeri AM,Sandid M,Ray AS,Fidler ME,Alexander MP,Larsen CP,Nasr SH	

View more IHC references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.